

Juniper CTP-SFP-1GE-SX Compatible SFP Module - 1000BASE-SX - 1GbE Multimode Fiber MMF Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 550m - 850nm - DDM

Product ID: CTPSFP1GESXS



The CTPSFP1GESXS is a Juniper CTP-SFP-1GE-SX compatible fiber transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000Base-SX compliant networks, with a maximum distance of up to 550 m (1804 ft).

Technical Specifications:

- **Wavelength:** 850nm
- **Maximum Data Transfer Rate:** 1000 Mbps (1 Gbps)
- **Type:** Multi Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 550 m (1804 ft)
- **MTBF:** 53,972,659 hours
- **Power Consumption:** Low power consumption

- **Digital Diagnostics Monitoring (DDM):** Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Features

- **100% JUNIPER CTP-SFP-1GE-SX COMPATIBLE SFP TRANSCEIVER:** Designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- **TECHNICAL SPECS:** 1000BASE-SX | 1Gbps | Multi Mode (MMF) | LC Connector | 850nm | Digital Diagnostic Monitoring (DDM) | Distances up to 550m (1804ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Juniper routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

	Warranty	Lifetime
Hardware	Compatible Brand	Juniper
Performance	DDM	Yes
	Fiber Operating Mode	Full-Duplex
	Max Transfer Distance	550 m (1804 ft)
	Maximum Data Transfer Rate	1.00 Gbps
	MTBF	53,972,659 hours
	Wavelength	850nm
Connector(s)	Connector A	1 - SFP Slot Plug
	Connector B	1 - Fiber Optic LC Duplex Female
Physical Characteristics	Product Height	0.5 in [1.2 cm]
	Product Length	2.6 in [65 mm]
	Product Width	0.6 in [14 mm]
	Weight of Product	2.5 oz [72 g]
Packaging Information	Package Height	0.6 in [15 mm]
	Package Length	9.1 in [230 mm]
	Package Width	8.1 in [207 mm]
	Shipping (Package) Weight	2.8 oz [80 g]
What's in the Box	Included in Package	1 - SFP Transceiver

Product appearance and specifications are subject to change without notice.