

## Standalone 1:5 USB Flash Drive Duplicator and Eraser – Flash Drive Copier

**Product ID:** USBDUP15



The USBDUP15 OnetoFive USB flash drive duplicator and eraser lets you quickly clone up to five backups of a single USB flash drive, or securely erase up to five flash drives, without connecting to a host computer.

Featuring a compact lightweight design that you can carry anywhere, and standalone operation that does not require a host computer, the flash drive duplicator and eraser has a small desktop footprint and is great for travel. Perfect for software and marketing content distribution in the office or on-the-go.

With an easy-to-read LCD display and intuitive four button menu operation, the USBDUP15 ensures hassle-free setup and control. The menu gives you push-button access to many value-added features that ensure simple task management such as: Capacity & Speed Check, Copy & Compare, Asynchronous Copy, and many more. It also provides numerous advanced setup options for experienced users.

This versatile device is both hard drive cloner and eraser in one, and offers two duplication modes (File & System Copy / Whole Copy) with up to 1.5GB/m at Whole Copy mode. It offers three erase modes (Quick Erase / Full Erase / DoD Erase) giving you the freedom to choose the best solution for your application.

The USBDUP15 is TAA compliant and backed by a 2-year StarTech.com warranty and lifetime technical support.

Note: The USBDUP15 flash drive duplicator supports copying/cloning to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a hard drive docking station or USB enclosure (sold separately)

## Certifications, Reports and Compatibility

### Applications

- Software and operating system updating and distributions
- Marketing collateral copying and distribution

- Rich media coping and distributions
- Quickly backup USB flash drives without a host computer
- Create exact copies of a USB flash drive in law enforcement and forensic investigations
- Thoroughly erase data from a flash drive, for added data security and peace of mind
- Clean and prepare USB drives for reuse
- Testing and evaluating USB drives

## Features

- Supports USB 3.0/2.0/1.1 flash drives
- 1:5 standalone duplication with 2 duplication modes
- Erase up to 5 USB flash drives with single-pass and multi-pass overwriting/DoD erasing
- High-speed duplication at up to 1.5GB per minute
- Compact, lightweight design
- TAA compliant
- Built-in LCD display
- Check drive capacity, quality and speed with intuitive task management
- Supports both Asynchronous and Synchronous copy modes, for quick batch swapping with 64 MB of internal memory

---


### Hardware

Warranty	2 Years
Bus Type	USB 2.0
Number of Drives	6
Compatible Drive Types	USB Flash Drive
Drive Installation	Removable
Buffer Size	64 MB

---

### Performance

Erase Modes	Quick Erase
-------------	-------------



1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear)

3-Pass Overwrite

Duplication Modes      System and File  
Sector by Sector (Whole Drive)

Duplication Speed      1.5GBpm

Max Drive Capacity      2TB

MTBF      176,549 hours

**Connector(s)**

Drive Connectors      USB Type-A (4 pin) USB 2.0

**Software**

OS Compatibility      OS independent; No software or drivers required

**Special Notes / Requirements**

System and Cable Requirements      For duplication, the destination drives must be of equal or greater capacity than the source drive.

Supports copying/cloning/erasing to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure (sold separately) if supported by the storage media

**Indicators**

LED Indicators      Green (Activity/Successful Copy)

Red (Error)

**Power**

Power Source      AC Adapter Included

Input Voltage      100 - 240 AC

Output Voltage      5 DC

Output Current      2

Center Tip Polarity      Positive

Plug Type      H



Power Consumption (In Watts) 10

---

**Environmental**

Operating Temperature 5C ~ 45C (41F ~ 113F)  
Storage Temperature -20C ~ 85C (-4F ~ 185F)  
Humidity 5% ~ 95% RH

---

**Physical Characteristics**

Color Black  
Material Plastic  
Product Length 6.6 in [16.7 cm]  
Product Width 4.7 in [12 cm]  
Product Height 1.0 in [25 mm]  
Weight of Product 11.2 oz [318 g]

---

**Packaging Information**

Package Length 9.1 in [23.1 cm]  
Package Width 7.1 in [18 cm]  
Package Height 3.2 in [82 mm]  
Shipping (Package) Weight 26.2 oz [742 g]

---

**What's in the Box**

Included in Package Duplicator  
  
Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand  
  
Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***