

5-Port USB Charging Station - 4 USB-A Auto-Sensing & 1 USB-C PD 3.0, USB-IF Certified, 110W Max

MODEL NUMBER: U280-005-WS4C1



Charges up to 5 USB devices, ranging from smartphones and tablets to power-intensive MacBooks and Amazon Kindles, at the same time.

Features

Portable USB Charging Station Charges Up to 5 Devices at the Same Time

At home or in the office, this USB charging station provides enough power and ports to keep your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. This compact charging station charges up to five devices at the same time, including smartphones, tablets, MacBooks, Chromebooks and Amazon Kindles, at a maximum of 110W. It doesn't require a computer, so you can take it anywhere AC power is available.

Provides Plenty of Juice for Charging with Auto-Sensing Technology

Four BC 1.2-compliant USB-A ports are split into two banks, each capable of delivering up to 5V 2.4A (12W) of power—enough for fast-charging smartphones, tablets and other mobile devices. Built-in auto-sensing lets the port detect the connected device and automatically adjust the required power level accordingly for optimum charge and compatibility. For devices that are even more powerful, the USB-C port provides up to 20V 4.3A (86W) for battery-intensive devices like the MacBook Pro or Chromebook Pixel. The USB-C port supports PD 3.0 Charging, which is up to four times faster than conventional USB charging.

USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line Performance

This cable meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the U280-005-WS4C1 meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB peripherals, adapters and cables with top efficiency and safety.

Easy to Use with the Included Power Cord

To charge your USB devices, simply plug the included four-foot power cord into any standard AC outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries reach capacity.

Highlights

- Certified by USB-IF to ensure highest-grade construction and performance
- USB-C port charges PD 3.0 devices up to 4 times faster than normal USB charging
- Auto-sensing USB-A ports adjust charging power for optimum charge and compatibility
- Stops charging when connected device is at full capacity to protect battery from damage
- Connects to any NEMA 1-15R, 5-15R or 5-15R/20R AC outlet for immediate charging

Applications

- Charge up to 5 smartphones, notebooks, tablets, Amazon Kindles or other USB devices at the same time
- Perfect for homes with busy families, dorm rooms and offices with multiple mobile devices

System Requirements

- Power cord for 120V applications included. For 230V applications, you will need to provide an applicable 230V power cord (sold separately).

Package Includes

- U280-005-WS4C1 5-Port USB Charging Station
- C7 to NEMA 1-15P power cord,



4 ft.

- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332241030
Over Current Protection	Y
OUTPUT	
Charging Ports / Amps	(4) 2.4A; 3A / 4.3A
Output Capacity	USB-A: 5V 4.8A (24W) total (5V 2.4A per port, 5V 2.4A (12W) simultaneous use per bank); USB-C: 5V 3A (15W), 9V 3A (27W), 12V 3A (36W), 15 3A (45W) and 20V 4.3A (86W); USB-A and USB-C total: 110W
Charging Method	USB
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60Hz
BATTERY	
Battery Charging (1.2 Port)	Yes
PHYSICAL	
Color	Black
Material of Construction	Plastic
Unit Dimensions (hwd / cm)	16 x 7.6 x 2.8
Unit Dimensions (hwd / in.)	6.3 x 3 x 1.1
Unit Packaging Type	Box
Unit Weight (kg)	0.36
Unit Weight (lbs.)	0.8
ENVIRONMENTAL	
Operating Temperature Range	32°F to 95°F / 0°C to 35°C
Storage Temperature Range	-4°F to 185°F / -20°C to 85°C
BTUs	1.02
Power Consumption (Watts)	0.3 (No Load)



Operating Humidity Range	5% to 95% RH, NON-CONDENSING
Storage Humidity Range	20% to 90% RH, NON-CONDENSING
CONNECTIONS	
Ports	5
Side A - Connector 1	IEC-320-C8
Side B - Connector 1	USB Type-C (FEMALE)
Side B - Connector 2	(4) USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	USB
CERTIFICATIONS	
Certifications	UL/cUL, FCC, USB-IF, RoHS, REACH
Approvals	UL Listed, USB-IF
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>