

## 2 Port Professional PS/2 KVM Switch

Product ID: SV231



This 2 Port PS/2 KVM Switch is a reliable computer management tool that allows you to control multiple computers from one source, minimizing downtime by making connected computers and input devices available as soon as they are attached.

This sturdy PS/2 KVM Switch features an all-metal, 1U chassis that adds to the unit's reliability and dependability.

The PS/2 KVM switch is designed to work with Dell, Compaq, IBM and HP servers, all PC notebook computers, and Compaq Alpha systems, and supports resolutions of up to 1920x1440 - ensuring a smooth and broadly compatible operating experience.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Manufacturing line computer control
- PC test/burn-in computer control
- Dual system control for a single workstation

### Features

- A dependable 3-year warranty provides peace of mind.
- Hot-pluggable to allow computers to be added or removed without worrying about having to reboot the other connected systems.
- Designed for guaranteed compatibility with Dell, Compaq, IBM and HP servers and systems.
- Compatible with all notebook computers.
- Compatible with Compaq Alpha systems.
- "Keep-alive" feature draws power from PC keyboard ports if power is lost. Switch will continue to operate during a power outage retaining complete control of all connected systems.
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets.
- Fast switch-buttons for each port provide quick access to any connected system.
- High 1920x1440 resolution capability supports the most demanding applications.
- Uses standard off-the-shelf cables or StarTech.com tangle-free KVM cables to connect PCs to the switch
- All cables connect to the back of the switch reducing space requirements
- Completely operating system independent. No software or drivers required.

<b>Hardware</b>	Warranty	3 Years
	Audio	No
	Cables Included	No
	Daisy-Chain	Yes
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	PS/2
	PC Video Type	VGA
	Rack-Mountable	No
<b>Performance</b>	DVI Support	No
	Hot-Key Selection	Yes
	IP Control	No
	Maximum Analog Resolutions	1920 x 1440
	Maximum Cascaded Computers	4
	Maximum Number of Users	1
	MTBF	111000 hours
	On-Screen Display	No
	Port Selection Support	Push Button and Hotkeys
<b>Connector(s)</b>	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 2 - PS/2 (6 pin, Mini-DIN) Female
	Host Connectors	2 - VGA (15 pin, High Density D-Sub) Male 4 - PS/2 (6 pin, Mini-DIN) Female
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Environmental</b>	Humidity	0~80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 60°C (14°F to 140°F)
<b>Physical Characteristics</b>	Enclosure Type	Steel
	Product Height	1.6 in [4 cm]
	Product Length	2.8 in [70 mm]
	Product Width	4.9 in [12.4 cm]
	Weight of Product	15.1 oz [427 g]

<b>Packaging Information</b>	Package Height	2 in [52 mm]
	Package Length	5.9 in [15.1 cm]
	Package Width	8.5 in [21.7 cm]
	Shipping (Package) Weight	21.7 oz [614 g]
<b>What's in the Box</b>	Included in Package	1 - 2 Port StarView 2 KVM Switch
		2 - PS/2 Mouse Connectors
		4 - Rubber feet
		1 - Hot-key Quick Reference
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.