

Bulk Cat6a Cable - 1000 ft. - Solid - CMR-Rated - Blue

Product ID: WIRC6ASPATBL



This bulk Cat6a cable meets or exceeds all Category 6a cable specifications to ensure reliable 10Gb network connections. The cable is shielded to protect your network against electromagnetic interference (EMI/RFI) and system noise, providing the perfect solution for fast and safe network connections.

Each cable is tested for up to 500MHz frequency and is more than suitable for 10GBase-T Ethernet networks.

Constructed with 100% copper and foil-shielded, twisted-pair wiring, this cable was built for quality performance. The cable is designed to keep the data signals traveling through your network free from interference and is perfect in environments that are prone to large amounts of EMI.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

Each of our cables is manufactured using high-quality copper conductors and they are carefully constructed and tested, to keep Near-End Crosstalk (NEXT) well within acceptable limits.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet and 4K or 1080p video streaming, using cables that include 23 AWG copper.

The WIRC6ASPATBL delivers reliable performance and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Designed for riser installation runs such as in walls, between floors and elevator shafts where CMR fire rating is required
- Deliver data, voice and video over 10 Gigabit networks

Features

- Protect your data against noise and EMI/RFI interference
- UL Listed CMR Riser Fire Rating
- Supports reliable 10Gbps Ethernet network connections
- High-quality 23 AWG copper wire

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMR Rated (Riser)
Cable Type	S/FTP

Performance

Cable Rating	CAT6a - 10Gbit/s
--------------	------------------

Physical Characteristics

Color	Blue
Wire Gauge	23 AWG
Conductor Type	Solid Copper
Cable Length	1000.0 ft [304.9 m]
Cable OD	0.3 in [7.4 mm]
Product Length	1000.0 ft [304.9 m]
Product Width	14.8 in [37.7 cm]
Product Height	12.4 in [31.4 cm]
Weight of Product	40.2 lb [18.2 kg]

Packaging Information

Package Length	14.8 in [37.7 cm]
----------------	-------------------



Package Width	14.8 in [37.7 cm]
Package Height	12.4 in [31.4 cm]
Shipping (Package) Weight	42.9 lb [19.4 kg]

What's in the Box

Included in Package	roll of Cat6a cable
---------------------	---------------------

****Product appearance and specifications are subject to change without notice.***

