

## Thin Client Mount - VESA Mounting Bracket

**Product ID:** ACCSMNT



This thin-client mounting bracket provides an excellent space-saving solution, by letting you mount your thin-client PC or docking station to create a clutter-free workspace.

The versatile double-sided VESA mount offers several installation options, enabling you to mount your thin-client PC or dock to the back of your monitor or under your desktop, or clamp it to a monitor-mount pole. The mount supports 75x75, and 100x100 VESA mount compatibility, making it suitable for most monitors and monitor mounts.

This adjustable mount is ideal for holding an Intel NUC, Mac Mini, most small CPUs, thin clients, docking stations, or USB hubs that fit within the width adjustability of the mount (.7" to 2.8" / 17 mm to 70 mm). The PC mounting bracket is also great for mounting other devices behind displays such as wireless routers, modems, video extenders, and digital signage media players. The mount can support up to 11 lb. (5 kg). It also features an adjustable strap to help keep your devices secure, and rubber pads to secure products with non-parallel surfaces.

The open-frame design of the mount allows unrestricted access to your computer.

The ACCSMNT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Create a clutter-free work space in office, business, commercial and institutional environments
- Enhance your home office by maximizing your desktop space

### Features

- Save space and reduce cable clutter by mounting your thin-client PC or docking station to the back of your monitor, clamped to a monitor-mount pole, or under your desk
- Supports up to 11 lb. (5 kg)
- Adjustable width from .7" to 2.8" (17 mm to 70 mm)
- 75x75 and 100x100 VESA mount compatibility
- Rubber pads to prevent damage to your device
- Keep your device secure with the adjustable strap
- Easily access your computer with the open-frame design

---

#### Hardware

Warranty	5 Years
Mounting Options	Back of Monitor, Under Desktop, or Clamped to Monitor-Mount Pole
VESA Hole Pattern(s)	75x75 mm 100x100 mm

---

#### Special Notes / Requirements

Note	The adjustable mount is designed for holding small CPUs, thin clients, docking stations, or USB hubs that fit within the width adjustability of the mount: .7" to 2.8" (17 mm to 70 mm).
------	--

---

#### Physical Characteristics

Color	Black
Material	Steel and Plastic
Product Length	4.6 in [11.8 cm]
Product Width	3.1 in [80 mm]
Product Height	3.7 in [95 mm]
Weight of Product	23.5 oz [666 g]

---

#### Packaging Information

Package Length	6.9 in [17.5 cm]
Package Width	5.1 in [13 cm]



Package Height 3.7 in [95 mm]

Shipping (Package) Weight 27.4 oz [776 g]

---

**What's in the Box**

Included in Package	mounting bracket
	adjustable strap
	pole mount
	pads
	M5x25 mm screws
	M4x12 mm screws
	M4 nuts
	screws
	washers
	instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

