

USB-C Multiport Video Adapter - 3-in-1 - 4K 30Hz - Black

Product ID: CDPVGDVHDBP



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI or HDMI display.

Avoid the hassle of carrying different adapters for different displays with this 3-in-1 USB-C adapter. With VGA, DVI and HDMI output, you can connect your laptop to virtually any display.

The HDMI output on this USB-C video adapter supports UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The convenient plug-and-play USB-C dongle is the perfect travel accessory. Fitting easily into your laptop bag, and offering three video output options, the USB-C display adapter is an ideal solution for Bring Your Own Device (BYOD) applications, wherever you go.

The CDPVGDVHDBP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect to virtually any display while traveling
- Connect your BYOD laptop to a provided VGA, DVI or HDMI display at work or school
- Connect a VGA, DVI or HDMI monitor to your USB-C computer to use as a secondary monitor

Features

- Maximize your video compatibility with a 3-in-1 USB-C display adapter: USB-C to VGA, DVI, or HDMI
- Get astonishing picture quality with support for UHD resolutions up to 4K 30Hz
- Thunderbolt 3 and USB Type-C with DP Alt Mode Compatible
- Easy to set up, use, and store

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	DVI-I (Digital Only) - Single-Link
	HDMI - 1.4
	VGA

Performance

Video Revision	DisplayPort 1.2
Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920 x 1200 @ 60Hz
Maximum Digital Resolutions	3840 x 2160 @ 30Hz
Supported Resolutions	HDMI output: 3840 x 2160 (@ 30 Hz), 2560 x 1600, 2048 x 1280 (@ 60 Hz), 1920 x 1200, 1920 x 1080, 1280 x 720
	VGA and DVI output: 1920 x 1200 (@ 60 Hz), 1920 x 1080, 1280 x 720
Wide Screen Supported	Yes
Audio Specifications	HDMI - 7.1 Channel Audio
	DVI - No Audio Support
	VGA - No Audio Support
General Specifications	Only one video output is supported on the video adapter at a time. If

multiple connections are made, only one of the outputs will function.

Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
Connector B	HDMI (19 pin)
	DVI-I (29 pin)
	VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Note	Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85% RH

Physical Characteristics

Color	Black
Cable Length	5.9 in [15 cm]
Product Length	3.3 in [85.0 mm]
Product Width	1.8 in [45.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	1.8 oz [51.0 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.8 in [20.0 mm]
Shipping (Package)	1.9 oz [55.0 g]



Weight

**What's in the
Box**

Included in Package	USB-C travel adapter
---------------------	----------------------

****Product appearance and specifications are subject to change without notice.***

