



1U 19-inch Hinged Wall Mount Bracket

TC-WP1U (v1.0R)

- 1U 19-inch wall mount bracket
- Sturdy steel construction
- Hinged design for easy access
- Perfect for rack mounting patch panels and PDU power strips
- Use with TRENDnet TC-P24C6 and TC-P16C6 patch panels (sold separately)
- 14cm (5.5 in.) maximum depth
- 2-year warranty

TRENDnet's 1U 19-inch Hinged Wall Mount Bracket, model TC-WP1U, is ideal for rackmount equipment such as patch panels and PDU power strips. This 1U wall mount bracket features a hinged design for easy access to the back of the mounted equipment. Constructed of sturdy steel, this space-saving 1U wall mount bracket is perfect for compact installation environments lacking the space for a full-sized equipment rack.



Installation Flexibility

Hinged design provides full access to the back of mounted equipment for easy installation



1U Wall Mount

Space-saving 1U size is perfect for compact installation environments lacking the space for a full-sized equipment rack



19-inch Rackmount Standard

Ideal for rackmount equipment such as patch panels and PDU power strips

Specifications

Features	<ul style="list-style-type: none"> • 1U 19-inch wall mount bracket • Hinged design for easy access • EIA-310-D standard compliance • Ideal for rack mounting patch panels and PDU power strips • Use with TRENDnet TC-P24C6 and TC-P16C6 patch panels (sold separately)
Materials	<ul style="list-style-type: none"> • SPCC steel construction
Dimensions	<ul style="list-style-type: none"> • 486 x 148 x 44.5mm (19.1 x 5.82 x 1.75 in.)
Weight	<ul style="list-style-type: none"> • 560g (19.75 oz.)
Warranty	<ul style="list-style-type: none"> • 2-year

PACKAGE CONTENTS

- TC-WP1U
- Mounting hardware
- Quick Installation Guide

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.