

2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch

Product ID: SV211USB



The SV211USB 2-Port VGA Cable KVM Switch lets you control two VGA, USB-equipped PCs with a single monitor, keyboard and mouse.

To help organize your desk without sacrificing valuable work space, this VGA USB KVM switch features a compact footprint and integrated KVM cables that can be connected directly to your systems. Plus, the KVM is USB-powered, eliminating the need for a bulky external power adapter and wall outlet.

This VGA KVM switch offers support for resolutions up to 2048x1536, for the ability to drive a high-resolution VGA display. For simple switching between connected systems, the KVM features a convenient push-button remote switch on a 1.5 meter (5ft) cable, as well as keyboard hot-key support and PC or Mac compatible switching software.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations, increasing user productivity in the office

Features

- Supports resolutions up to 2048x1536

- Switch PCs via push-button, hot-keys or switching software (included)
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac platforms
- USB Powered - No external power adapter required
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Hardware

| | |
|------------------------------|---------|
| Warranty | 2 Years |
| Audio | No |
| KVM Ports | 2 |
| PC Interface | USB |
| PC Video Type | VGA |
| Number of Monitors Supported | 1 |
| Rack-Mountable | No |
| Cables Included | Yes |
| Daisy-Chain | No |

Performance

| | |
|------------------------|------------------------------------|
| On-Screen Display | No |
| IP Control | No |
| Hot-Key Selection | Yes |
| Port Selection Support | Push Button, Hotkeys, and Software |

Connector(s)

| | |
|----------------------|--|
| Console Interface(s) | VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0 |
| Host Connectors | VGA (15 pin, High Density D-Sub) |



USB Type-A (4 pin) USB 2.0

Software

| | |
|------------------|--|
| OS Compatibility | Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2016, 2019 Mac OS 10.x (Tested up to 10.9), 9.x |
|------------------|--|

Special Notes / Requirements

| | |
|------|--|
| Note | OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform |
|------|--|

Indicators

| | |
|----------------|------------------------|
| LED Indicators | PC Selection indicator |
|----------------|------------------------|

Power

| | |
|--------------|-------------|
| Power Source | USB-Powered |
|--------------|-------------|

Environmental

| | |
|-----------------------|--------------------------|
| Operating Temperature | 0C to 40C (32F to 104F) |
| Storage Temperature | -20C to 60C (4F to 140F) |
| Humidity | 0~90% RH Non-Condensing |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Material | Plastic |
| Cable Length | 33.5 in [85 cm] |
| Product Length | 3.5 in [88 mm] |
| Product Width | 2.6 in [66 mm] |
| Product Height | 0.9 in [23 mm] |
| Weight of Product | 11.3 oz [321 g] |

Packaging Information

| | |
|----------------|----------------|
| Package Length | 9.8 in [25 cm] |
|----------------|----------------|



| | |
|---------------------------|------------------|
| Package Width | 6.5 in [16.4 cm] |
| Package Height | 2.5 in [63 mm] |
| Shipping (Package) Weight | 15.4 oz [435 g] |

What's in the Box

| | |
|---------------------|--------------------|
| Included in Package | KVM Switch |
| | Software CD |
| | Instruction Manual |

****Product appearance and specifications are subject to change without notice.***

