

USB Dual VGA over Cat5 KVM Console Extender - 650 ft / 200m

Product ID: SV565DUTPU



The SV565DUTPU USB Dual VGA KVM Console Extender over CAT5 UTP lets you Operate a Dual VGA PC or KVM switch up to 650ft (200 m) away, as if it was installed locally, at high-definition 1920x1200 resolution. PC connection cables are included with this product for a ready to use solution.

The dual VGA cat5 KVM extender supports easy to use hot-key and push button commands which allow you to switch between local and remote connected systems, while console connections at both ends of your setup provide easy access to all connected systems from either location. The hot-key commands also provide video adjustment controls for optimizing picture quality over varying distances. Extending over two standard Cat 5 (or better) cables gives you the ability to use existing infrastructure wiring to achieve remote access to your server or KVM switch.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for controlling a PC in an area where fan or hard drive noise is unacceptable such as a television broadcast studio
- Control/Monitor a remote server from a harsh environment where the PC would not function properly due to heat/dust/etc. (factory, warehouse, mining, etc.)
- Can act as a thin client for power users controlling powerful rack mounted servers as their desktop machines
- Use one or more servers in a server room from a remote location within the same building or campus

Features

- Dual VGA KVM extender at 1920x1200 resolution
- Can be used with a single computer or connected to an existing KVM switch
- Extend up to 650 ft. (200 m) using 2 industry-standard UTP network cables
- KVM console connections available on both the local and remote end
- Supports most combo keyboard and mouse sets (including Wireless)
- Intuitive hot-key commands for fine-tuning video

Hardware

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	2
Rack-Mountable	No
Cables Included	Yes

Performance

IP Control	No
Max Transfer Distance	200 m (656 ft)
Maximum Analog Resolutions	1920x1200
Supported Resolutions	1920x1200 @ 650 ft (200m)
MTBF	65000 hours

Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub)
	USB Type-A (4 pin) USB 2.0
Host Connectors	VGA (15 pin, High Density D-Sub)



Other Interface(s) RJ-45

Software

OS Compatibility OS independent; No software or drivers required

Special Notes / Requirements

Note Product weights/measurements and connector types indicate a single unit only (either Host or Remote)

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 0.2A

Output Voltage 9V DC

Output Current 0.6A

Center Tip Polarity Positive

Plug Type M

Power Consumption (In Watts) 5.4

Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -10C to 60C (14F to 140F)

Humidity 0~80% RH

Physical Characteristics

Color Black

Material Steel

Product Length 6.1 in [15.5 cm]

Product Width 3.1 in [80 mm]

Product Height 1.6 in [40 mm]



Weight of Product 18.9 oz [535 g]

Packaging Information

Package Length 14.4 in [36.7 cm]

Package Width 9.4 in [23.9 cm]

Package Height 3.0 in [75 mm]

Shipping (Package) Weight 5.0 lb [2.3 kg]

What's in the Box

Included in Package

- local unit
- remote unit
- 6 ft 2-in-1 USB VGA KVM cables
- universal power adapter (NA/EU/UK/AU)
- rubber feet
- instruction manual

****Product appearance and specifications are subject to change without notice.***

