

Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Blue

**Product ID:** WIRC5ECMR



The WIRC5ECMR Cat5e 350MHz Solid UTP Cable (Blue) is CMR rated for use in walls, conduit, ceilings, etc. and is packaged as a 1000-foot bulk roll. The cable features a blue PVC jacket, which provides both flexibility and durability, while making it easier to color code network cable connections.

Backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- CMR rated for use in walls, conduit, ceiling and other vertical applications
- Ideal for network installation at home, office, or educational institution

### Features

- UL Listed CMR Riser Fire Rating
- Rated up to 350Mhz to provide superior performance and bandwidth over the standard 100Mhz Category 5e specifications
- Flexible PVC rated jacket
- 24 AWG solid bare copper conductor
- 4-pair unshielded twisted pair (UTP) cable

- Foot-marked cable

---

#### Hardware

Warranty	Lifetime
Number of Conductors	4 Pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMR Rated (Riser)
Industry Standards	Category 5 CMR

---

#### Performance

Maximum Cable Length	1000.0 ft [304.9 m]
----------------------	---------------------

---

#### Physical Characteristics

Color	Blue
Wire Gauge	24 AWG
Conductor Type	Solid Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Weight of Product	20.6 lb [9.3 kg]

---

#### Packaging Information

Package Length	14.0 in [35.5 cm]
Package Width	8.5 in [21.7 cm]
Package Height	13.9 in [35.2 cm]
Shipping (Package) Weight	21.0 lb [9.5 kg]

---

#### What's in the Box

Included in Package	1000 ft Bulk Roll of Blue CMR Cat5e Solid UTP Cable
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*

