

Travel A/V adapter: 3-in-1 DisplayPort to VGA DVI or HDMI converter

**Product ID:** DP2VGDVHD



The DP2VGDVHD DisplayPort to VGA, DVI or HDMI converter offers a compact 3-in-1 solution for connecting your DP-equipped desktop, laptop or Ultrabook computer to a VGA, DVI, or HDMI display.

Compatible with almost any display, television or projector, this versatile converter provides the ideal plug-and-play solution for travel or BYOD (Bring Your Own Device) applications around the office. With three of the most common interfaces to choose from, the converter equips you to walk into any boardroom ready to connect to an available display device, even if you don't know what connection ports will be available.

For seamless connections from your DisplayPort-equipped computer, the converter supports video resolutions up to 1920x1200/1080p, so you can convert a DisplayPort video source to VGA, HDMI, or DVI without sacrificing video quality.

The DisplayPort converter offers a small footprint and lightweight design that makes it easy to keep on hand without it taking up too much space in your laptop bag.

The DP2VGDVHD is backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Keep the adapter with you while traveling, to connect to virtually any display
- Connect your BYOD laptop/Ultrabook to a provided HDMI, DVI, or VGA display at work
- Connect a DVI, VGA, or HDMI display to your DisplayPort computer, to use as a secondary monitor

## Features

- Three-in-one adapter - DP to: VGA, DVI, HDMI
- Support for video resolution up to 1920x1200/1080p
- Plug-and-play installation
- Small footprint
- Portable, lightweight construction

---

## Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2
AV Output	DVI-D - Single-Link
	HDMI - 1.4
	VGA
Audio	Yes
Chipset ID	NXP Semiconductors PTN3392BS
	Parade Technologies Inc. PS8312

---

## Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920x1200/1080p
Maximum Digital Resolutions	1920x1200/1080p
Wide Screen Supported	Yes
Audio Specifications	DVI - No Audio Support
	HDMI - 7.1 Channel Audio
	VGA - No Audio Support

---

## Connector(s)



Connector A	DisplayPort (20 pin)
Connector B	DVI-D (25 pin)
	VGA (15 pin, High Density D-Sub)
	HDMI (19 pin)

---

### Special Notes / Requirements

Note	<p>Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.</p> <p>The HDMI port is a passive port.</p> <p>The DVI-D is a passive port.</p> <p>The VGA port is an active port.</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p>
------	--

---

### Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10%-85%RH

---

### Physical Characteristics

Color	Black
Cable Length	5.9 in [15 cm]
Product Length	10.5 in [26.6 cm]
Product Width	1.8 in [45.0 mm]
Product Height	0.8 in [20.0 mm]
Weight of Product	2.3 oz [65.0 g]

---

### Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.7 in [17.0 mm]



Shipping (Package) Weight	2.6 oz [73.0 g]
------------------------------	-----------------

---

**What's in the  
Box**

Included in Package	DisplayPort to HDMI/VGA/DVI Adapter
	Installation Guide

---

***\*Product appearance and specifications are subject to change without notice.***

