

Space constraints are no obstacle to infection control. Our hygienic white Slim Cool Low Profile keyboard is fully sealed, seamless and long term resistant to cleaning with surface disinfectants, but only needs 14cm x 30 cm of your valuable space.

Thanks to its Tru Lock locking mechanism, one touch is all it takes to prevent unwanted commands or screen gibberish during a clean. The USB cable can stay connected. . We understand that cleaning can go beyond a quick wipe.

You can go ahead and submerge our medical keyboards for a more thorough disinfection. Our medical keyboards comply with the industry standards for your electrical and operational safety. All of this without compromising usability.

7 Requirements for a Medical Grade Keyboard

- Fully sealed
- Disinfectable
- Hygienic white
- Lockable
- Easy to use
- Electrically safe
- No drop hazard

key height optimized for easy- wipe cleaning combined with the modern typing feeling of a laptop.

Specifications

- Compliance: IP 68, CE, FCC, EN-IEC 60601-1, WEEE, RoHs
- Colour: hygienic white
- Size: 30 x 14 x 1.5 cm
- Weight: 600 g
- Cable Length: approx. 180 cm
- Storage temperature: -20° to 70°C
- Operating temperature: 0° to 70°C
- Power Consumption: 26mA (Max)
- Platform: Windows, Mac and Linux
- Layout: Includes 12 Function keys





Backlight - Individually illuminated keys enable accurate typing in low-light conditions.



MagFix - Secures your keyboard hygienically to a sloping or fold-up tray.



Smart Cable - Cables can be customized in length. Ask for the options.

Other medical products



The Slim Cool Low Profile keyboard sets itself apart by its

- Slim Cool model
- Really Cool model

Mice





The Key to Infection Control! sales@mmieu.com • www.man-machine.com • (+31) 23 5450185