

## 2 Port DVI Video Splitter with Audio

**Product ID:** ST122DVIA



The ST122DVIA DVI splitter lets you share one DVI video and audio source on two displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source.

With support for high definition resolutions up to 1080p (HDTV)/1920x1200 (PC), the DVI splitter delivers a simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments).

The DVI video splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

This product is TAA compliant and backed by StarTech.com's 2-year warranty with FREE lifetime tech support.

## Certifications, Reports and Compatibility

### Applications

- Connect DVI projectors, monitors, large displays, and wall display systems for digital signage applications and ensuring content is delivered to target audience.
- Great for use in tradeshows, POS retail, healthcare, transportation terminals, education, house of worship.

### Features

- Supports resolutions of up to 1920 x 1200 pixels @ 60 Hz
- Split both video and 3.5mm analog stereo audio

- DVI, and HDCP compliant for easier HD video distribution
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion
- Easy setup for a quick connection in minutes

---

#### Hardware

Warranty	2 Years
Ports	2
AV Input	DVI
AV Output	DVI
Cabling	DVI
Industry Standards	DVI 1.0, and HDCP 1.1

---

#### Performance

Max Distance	10 m / 33 ft
Maximum Digital Resolutions	1920x1200 @ 60Hz
Wide Screen Supported	Yes

---

#### Connector(s)

Connector A	DVI-I (29 pin)
	3.5 mm Mini-Jack (3 Position)
Connector B	DVI-I (29 pin)
	3.5 mm Mini-Jack (3 Position)

---

#### Indicators

LED Indicators	Green - Power/Link
	Green - Link

---

#### Power

Power Source	AC Adapter Included
Input Current	0.6A
Output Voltage	12V DC



Output Current	1.5A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	18W

---

#### Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~80% RH

---

#### Physical Characteristics

Color	Black
Material	Aluminum
Product Length	7.1 in [18.1 cm]
Product Width	3.4 in [85.2 mm]
Product Height	0.8 in [20.0 mm]
Weight of Product	14.2 oz [401.0 g]

---

#### Packaging Information

Package Length	8.7 in [22.1 cm]
Package Width	4.0 in [10.2 cm]
Package Height	3.9 in [98.0 mm]
Shipping (Package) Weight	25.8 oz [732.0 g]

---

#### What's in the Box

Included in Package	DVI splitter
	rubber feet
	universal power adapter (NA, EU, UK, ANZ)



instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

