

12U 19" Open Frame Server Rack - 4 Post Adjustable Depth 23-41" Mobile - Free Standing Rolling Network/Computer Equipment Data Rack - Dell PowerEdge HP ProLiant ThinkServer (4POSTRACK12U)

Product ID: 4POSTRACK12U



The 4POSTRACK12U 12U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 12U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

Features

- **ADJUSTABLE DEPTH:** 12U Open frame rack with four vertical rails rack for servers & network equipment w/ adjustable mounting depth 23" to 41" (59cm to 104cm); maximize available space with 25" (64 cm) height, for integration in utility or server closet
- **EASY ASSEMBLY:** Mobile computer equipment rack with assembly instructions & easy-to-follow online video; compact flat pack shipping/packaging design to avoid damage and facilitate problem-free installations
- **COLD ROLLED STEEL:** Durable 4 Post 19" EIA/ECA-310-E open frame designed for ventilation with 12U mounting height, 1200lb (544lbs) capacity, 3 install options included: casters, levelling feet, or base-plate to secure rack to the floor
- **HARDWARE INCLUDED:** Rolling rack with cage nuts & screws to mount equipment, easy to read Units (U) & depth adjustment markings, cable management hooks for organization, with required assembly tools
- **STARTECH.COM ADVANTAGE:** Trusted by IT professionals for a variety of applications, this rack supports server depth equipment and can be used for servers, UPSs, patch panels, switches, and other networking or AV equipment. StarTech.com 2 Year Warranty and Free Lifetime Technical Support

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	12U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Built-in Cable Management
	Casters (Included)
	Easy Assembly
	Grounding Lug(s)
	Leveling Feet
	U-Markings
Mounting Rail Profile	L-Shape

Mounting Hole Types Square (For Cage Nut)

Industry Standards EIA/ECA-310-E

Performance

Weight Capacity (Stationary) 19.2 oz [544 g]

Physical Characteristics

Color Black

Construction Material Steel

Product Measurements

Product Length 3.4 ft [1.0 m]

Product Width 23.8 in [60.4 cm]

Product Height 25.1 in [63.8 cm]

Weight of Product 50.3 lb [22.7 kg]

Maximum Mounting Depth 3.3 ft [1.0 m]

Minimum Mounting Depth 22.0 in [56 cm]

Product Height with Casters 28.0 in [71 cm]

Packaging Information

Flat Pack (Assembly Required) Yes

Package Length 25.6 in [65.0 cm]

Package Width 14.2 in [36.1 cm]

Package Height 6.3 in [16.0 cm]

Shipping (Package) Weight 58.2 lb [26.3 kg]

What's in the Box

Included in Package Left Vertical Rail

Right Vertical Rail

Base Bracket

Corner Section

Center Section

Top Bracket

M8 Bolt

M8 Washer

M8 (13mm) Wrench

M6 (10mm) Wrench

Phillips Screwdriver

M6 Cage Nut

PVC Cup Washer

M6 Phillips Head Screw

Cable Management Hook

Hook Mounting Screw

Casters

Leveling Feet

M6 Screw

M6 Flat Washer

M6 Flange Nut

Grounding Wires

****Product appearance and specifications are subject to change without notice.***

