

# USB C Multiport Video Adapter with HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 1.4 or mDP 1.2 (4K) - VGA or DVI (1080p) - Space Gray Aluminum

Product ID: CDPVDHMDPSG



This space gray USB-C™ multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI® or Mini DisplayPort display. The adapter is also available in [silver \(CDPVGDVHMDMP\)](#) and [rose gold \(CDPVDHMDMPRG\)](#).



### All-in-One Video Connectivity with Travel in Mind

Avoid the hassle of carrying different adapters for different displays with this 4-in-1 USB-C adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.



### Astonishing Picture Quality

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

## Stylish Connectivity

The USB Type-C adapter has an aluminum housing designed to match your space gray MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

The CDPVDHDMMDPSG is backed by a StarTech.com 3-year warranty and free lifetime technical support.



### Certifications, Reports and Compatibility



### Applications

- Connect to virtually any display while traveling
- Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook

### Features

- 4-IN-1 MULTIPORT USB-C VIDEO ADAPTER: USB-C DP Alt Mode to any one of HDMI 1.4 (4K 30Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible
- TOUGH & PORTABLE: Durable aluminum Space Gray enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms
- COMPATIBILITY: USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Laptop 3/Surface Book 3, TB3 MacBook Pro/Air, HP EliteBook/Spectre/ZBook, Chromebooks
- TESTED & VERIFIED: USB Type-C adapter tested @ 4K mini DisplayPort (60Hz)/HDMI (30Hz) or 1080p VGA/DVI with TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- EASY TO USE: Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

<b>Hardware</b>	Warranty	3 Years	
	Active or Passive Adapter	Active	
	Adapter Style	Adapters	
	AV Input	USB-C	
	AV Output	HDMI - 1.4 Mini DisplayPort - 1.2 DVI-I (Digital Only) - Single-Link VGA	
	Chipset ID	Cypress - CYPD1120 Cypress - CY7C65210 Parade - PS8348B Parade - PS171	
	<b>Performance</b>	Audio Specifications	HDMI - 7.1 Channel Audio DVI - No Audio Support VGA - No Audio Support Mini DisplayPort - 2 Channel Audio
Maximum Analog Resolutions		1920 x 1200 @ 60Hz	
Maximum Cable Distance To Display		49.9 ft [15.2 m] HDMI 49.9 ft [15.2 m] DVI 49.9 ft [15.2 m] Mini DisplayPort	
Maximum Digital Resolutions		3840 x 2160 @ 30Hz	
MTBF		654,111 hours	
Supported Resolutions		<b>Max HDMI output:</b> 3840 x 2160 @ 30Hz <b>Max mDP output:</b> 3840 x 2160 @ 60Hz <b>HDMI and mDP output:</b> 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720 <b>DVI and VGA output:</b> 1920 x 1200, 1920 x 1080, 1280 x 720	
Video Revision		DisplayPort 1.2	
Wide Screen Supported		Yes	
<b>Connector(s)</b>		Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
		Connector B	1 - Mini-DisplayPort (20 pin) Female Output

		1 - VGA (15 pin, High Density D-Sub) Female Output 1 - DVI-D (25 pin) Female Output 1 - HDMI (19 pin) Female Output
<b>Special Notes / Requirements</b>	<b>Note</b>	Only one video output is supported on the video adapter at a time, if multiple connections are made, only one of the outputs will function  Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling
<b>Environmental</b>	Humidity	<b>Storage:</b> 5% ~ 90 % RH (no condensation) <b>Operating:</b> 10% ~ 85 % RH (no condensation)
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	4.3 in [110 mm]
	Color	Space Gray
	Material	Aluminum
	Product Height	1.2 in [3 cm]
	Product Length	6.9 in [17.5 cm]
	Product Width	5.7 in [14.5 cm]
	Weight of Product	6.4 oz [180 g]
<b>Packaging Information</b>	Package Height	0.6 in [16 mm]
	Package Length	2.2 in [55 mm]
	Package Width	4.1 in [10.5 cm]
	Shipping (Package) Weight	0.3 lb [0.1 kg]
<b>What's in the Box</b>	Included in Package	1 - travel A/V adapter

Product appearance and specifications are subject to change without notice.