

42U Server Rack Cabinet - 4-Post Adjustable Depth (3" to 35") IT Network Equipment Rack Enclosure with Casters/ Vented/Locking /3315lb /Dell PowerEdge HP ProLiant ThinkServer

Product ID: RK4242BK24



This 42U server rack cabinet provides security for storing standard 19" rack-mount equipment. The rack is compatible with EIA-310 compliant equipment and supports a weight capacity of 3315 lb. (1500 kg).

Easy Equipment Installation

This computer rack cabinet ships fully assembled and ready to use with:

- 200 M6 cage nuts and screws
- Two 0U tool-less mounting panels
- Hook-and-loop tie
- Casters for portability

The mounting rails can be adjusted from 3 to 35 in. (76.2 mm - 800 mm) to support full-depth equipment installations and the extra width and depth provide space for additional cable and power management.

Keep Equipment Secure, Cool, and Accessible

This rack features front and rear locking mesh doors to keep your equipment secure awhile increasing airflow to promote passive cooling. The removable side panels with independent quick-release locks provide access to your equipment easily while keeping it secure.

Maximum Maneuverability

The portable server rack enclosure features casters, providing ease of mobility around your server space. The width and height of the rack fit through standard doorways, giving you the freedom to wheel your server rack into different rooms as needed.

StarTech.com offers a wide selection of products that help you to optimize your server rack storage space. This mobile server rack cabinet is backed by a 5-year warranty and free lifetime North American based technical support.

Certifications, Reports and Compatibility



Applications

- Broadcasting equipment
- Mount servers and KVM switches
- Deploy to maximize space
- Keep equipment secure

Features

- FULL SIZED SECURE RACK: 19" 4 post 42U server rack cabinet w/adjustable depth of up to 35", internal depth 41.4", dual panel doors make equipment easily accessible; Locking doors/sides (2 keys inc.)
- FULLY ASSEMBLED WITH CASTERS: Pre-built w/casters and levelling feet to offer manoeuvrability & stability; 200 cage nuts/screws, and hook & loop tape provided so that equipment can easily be mounted
- DESIGN AND VENTILATION: Free standing data cabinet w/strong mesh doors & vented top allow for abundant airflow & top is also removeable to run cables; 1U intervals are marked for easy identification
- COMPATIBILITY: EIA/ECA-310-E Compliant for server/networking equipment, incl. brands like HPE ProLiant, Dell PowerEdge & Lenovo ThinkSystem; Split rear doors reduce rear access space requirements
- SPECS: 5 year warranty | Rolling/Mobile 42U 19in cabinet enclosure | Mounting depth 3 to 35" | 3,315lb/1,500kg stationary capacity | 200xM6 Cage nuts/screws | 10ft/3m hook & loop tape | Grounding lugs

Hardware	Warranty	5 Years
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel Mesh
	Front Door Features	Secure Key Lock with Removable Front Door
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	G-Shape
	Rack Type	4-Post
	Rear Door Construction	Steel Mesh
	Side Panel Construction	Steel
	Side Panel Features	Secure Key Lock with Removable Side Panels
	Special Features	Adjustable Mounting Rails
		Built-in Cable Management
		Casters (Included)
Grounding Lug(s)		
Leveling Feet		
Ships Fully Assembled		
U-Markings		
U Height	42U	
Wallmountable	No	
Performance	Weight Capacity (Stationary)	3315 lb [1500 kg]
Physical Characteristics	Color	Black
	Rear Door Features	Secure Key Lock with Removable Back Door
Product Measurements	Internal Depth	41.4 in [105.2 cm]
	Internal Width	23.6 in [60 cm]
	Maximum Mounting Depth	35 in [89 cm]
	Minimum Mounting Depth	5.2 in [13.2 cm]
	Product Height	77.2 in [196 cm]
	Product Height with Casters	78.5 in [199.4 cm]
	Product Length	41.6 in [105.6 cm]

	Product Width	23.8 in [60.4 cm]
	Weight of Product	285.1 lb [129 kg]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	7 ft [2.1 m]
	Package Length	3.9 ft [1.2 m]
	Package Width	26.6 in [67.5 cm]
	Shipping (Package) Weight	373.5 lb [169 kg]
What's in the Box	Included in Package	1 - Server Rack Cabinet
		200 - M6 Cage Nuts
		200 - M6 Screws
		200 - Plastic Cup Washers
		1 - Hex Key
		2 - Keys
		1 - 10 ft. [3 m] Hook and Loop Tape
	1 - User Manual	

Product appearance and specifications are subject to change without notice.