

Fiber Optic Cable - 10 Gb Aqua - Multimode Duplex 50/125 - LSZH - LC/SC - 2 m

StarTech ID: A50FBLCSC2



The A50FBLCSC2 2-meter (6.6ft), 10 Gigabit, Aqua Multimode 50/125 Duplex LSZH Fiber Patch Cable is terminated with one LC (male) connector and one SC (male) connector and is composed of 50/125 micron OM3 aqua fiber to deliver reliable data transfers at blinding speeds making it perfect for fiber cable runs between multiple backbone switches, hubs and routers as well as higher end networking equipment.

Suited for a broad range of environments, A50FBLCSC2 is housed in a flame retardant, LSZH (Low-Smoke, Zero-Halogen) cable jacket, taking safety to a new level by ensuring minimal smoke, toxicity and corrosion in the event of a fire – making it the best choice for a wide range of environments, including industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Applications

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication / Data communication
- Used in 10 Gigabit high speed network environments

Features

- A more durable cable design
- A solution that is cost effective and supports longer distances
- Attenuation loss meets or exceeds industry standards
- Designed to be used in 10 Gb Ethernet applications

Technical Specifications

Warranty	Lifetime
Fiber Size	50/125
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Cable Rating	Fiber - 10 Gbit/s
Fiber Classification	OM3
Fiber Type	Multi Mode
Maximum Data Transfer Rate	10Gbps
Wavelength	850nm
Connector A	1 - Fiber Optic LC Duplex Male
Connector B	1 - Fiber Optic SC Duplex Male
Cable Length	6.6 ft [2 m]
Color	Aqua
Diameter	3mm
Product Length	6.6 ft [2 m]
Product Weight	1 oz [28 g]
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 2m 10 Gb Aqua Multimode 50/125 Duplex LSZH Fiber Patch Cable LC - SC

Certifications, Reports and Compatibility

