

USB PS2 KVM Console Extender Cat5 Extender - 500 ft

**Product ID:** SV565UTP



The SV565UTP USB PS2 KVM console extender lets you control a server, computer or multiple computers (connected through KVM switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away.

Use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

For added convenience, the Console/KVM extender supports both USB and PS/2 computer connections, and is compatible with any brand of KVM Switch.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Access one or more servers located in a secure server room, from a remote location
- Monitor computer-controlled equipment in a factory or warehouse

### Features

- Can be used with a single computer or connected to an existing KVM switch
- Easy installation using industry-standard UTP network cable

- Supports a max. extension distance of 500 ft (150 m)
- Supports auto-switching between host and remote users or dedicated control
- Compatible with USB and PS/2 computers at the host and remote locations (PS/2 keyboard and mouse required for remote console)
- Intuitive hotkey commands

---

#### Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB and PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No

---

#### Performance

IP Control	No
Max Transfer Distance	150 m (492 ft)
Supported Resolutions	1280x1024 @ 300ft/ 100m 1024x768 @ maximum cable length
MTBF	126000 hours

---

#### Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub) PS/2 (6 pin, Mini-DIN)
Host Connectors	VGA (15 pin, High Density D-Sub)
Other Interface(s)	RJ-45

---

#### Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Special Notes / Requirements**

Note Product weights, measurements and connectors indicate a single unit only (either Host or Remote)

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.2A
Output Voltage	9V DC
Output Current	0.6A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	5.4

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~80% RH

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	3.0 in [75 mm]
Product Width	6.1 in [15.5 cm]
Product Height	0.8 in [20 mm]
Weight of Product	21.6 oz [613 g]

---

**Packaging Information**

Package Length	9.6 in [24.5 cm]
Package Width	11.7 in [29.7 cm]



Package Height 3.3 in [85 mm]

Shipping (Package) Weight 2.4 lb [1.1 kg]

---

**What's in the Box**

Included in Package	Local Unit
	Remote Unit
	Packs Rubber Feet
	Power Adapters
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

