

6 ft DVI to Coax High Resolution VGA Monitor Cable

Product ID: DVIVGAMM6



The DVIVGAMM6 6-foot DVI to VGA Monitor Cable features a DVI (analog) male connector and a VGA (High Density D-Sub) male connector, providing a cost-effective way to connect an analog or a dual mode Flat Panel Display to a PC or Mac computer with a DVI Analog Video Card.

Expertly designed and constructed of only high quality materials, the 6ft DVI to VGA Monitor cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connects PC/Mac with DVI Analog Video Card to an Analog or Dual-Mode Flat Panel Display

Features

- Manufactured according to DVI specifications
- Molded connector ends with strain relief

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Connector Plating	Nickel

Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	DVI-A (17 pin)
Connector B	VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	6.6 oz [186 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.3 in [34 mm]
Shipping (Package) Weight	6.9 oz [195 g]

What's in the Box

Included in Package	6 ft DVI to Coax High Resolution VGA Monitor Cable
---------------------	--

**Product appearance and specifications are subject to change without notice.*

