

6 ft IEEE-1394 FireWire Cable 9-6 M/M

**Product ID:** 1394\_96\_6



This 6ft IEEE 1394b FireWire 800 Cable provides one FireWire 9-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 800Mbps, FireWire 800 (IEEE 1394b) technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

This high quality FireWire 800 (9 to 6-pin) cable compatible with all 1394a & 1394b PC FireWire (400/800), Apple FireWire, and Sony iLink devices and is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

### Features

- Fast data transfer rate of up to 800 Mbits/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards

- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

---

**Hardware**

|                    |                   |
|--------------------|-------------------|
| Warranty           | Lifetime          |
| Industry Standards | IEEE 1394a, 1394b |

---

**Connector(s)**

|             |                                  |
|-------------|----------------------------------|
| Connector A | FireWire 800 (9 pin, IEEE 1394b) |
| Connector B | FireWire 400 (6 pin, IEEE 1394a) |

---

**Physical Characteristics**

|                   |                  |
|-------------------|------------------|
| Color             | Black            |
| Cable Length      | 6.0 ft [1.8 m]   |
| Product Length    | 6.0 ft [1.8 m]   |
| Product Width     | 0.0 in [0.0 mm]  |
| Product Height    | 0.0 in [0.0 mm]  |
| Weight of Product | 3.8 oz [106.7 g] |

---

**Packaging Information**

|                           |                  |
|---------------------------|------------------|
| Package Length            | 7.8 in [19.9 cm] |
| Package Width             | 0.7 in [17.0 mm] |
| Package Height            | 8.3 in [21.1 cm] |
| Shipping (Package) Weight | 3.8 oz [107.7 g] |

---

**What's in the Box**

|                     |                                       |
|---------------------|---------------------------------------|
| Included in Package | 6 ft IEEE-1394 FireWire Cable 9-6 M/M |
|---------------------|---------------------------------------|

---



*\*Product appearance and specifications are subject to change without notice.*

