

Computer Power Cord - NEMA 5-15P to C19, 14 AWG, 6 ft

Product ID: PXT515C19146



This NEMA 5-15P-to-C19 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for high-end server equipment such as routers, switches, Power Distribution Units (PDU), etc.

Plus, you can use the cable to extend the reach of your existing power cord by 6 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT515C19146 power cord is backed by a lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Connect your high-power server equipment to a power outlet
- Extend your existing power cord by 6 feet

Features

- Rated to carry 125V at 15A
 - 14 AWG wire
 - UL, RoHS compliant
-

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	NEMA 5-15 Power (North America)
Connector B	IEC 60320 C19 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	11.6 oz [328 g]

Packaging Information

Package Quantity	1
Package Length	11.4 in [29 cm]
Package Width	5.7 in [14.5 cm]
Package Height	2.0 in [52 mm]
Shipping (Package) Weight	11.8 oz [335 g]



**What's in the
Box**

Included in Package 6 ft 14 AWG Computer Power Cord - NEMA 5-15P to IEC 320 C19

****Product appearance and specifications are subject to change without notice.***

