

6ft HDMI Cable - 4K High Speed HDMI Cable with Ethernet - 4K 30Hz UHD HDMI Cord - 10.2 Gbps Bandwidth - HDMI 1.4 Video / Display Cable M/M 28AWG - HDCP 1.4 - Black

Product ID: HDMIMM6HS



The HDMIMM6HS 6-foot High Speed HDMI Cable with Ethernet supports the advanced capabilities of the High-Definition Multimedia Interface, including Ethernet data inter-connectivity with compatible HDMI-enabled products, and is fully backward compatible with older HDMI-capable devices.

The cable features gold-plated HDMI (male) connectors which help to ensure a high quality digital connection capable of transmitting high-definition video and multi-channel audio between devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, stereo receivers and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

All StarTech.com High Speed HDMI Cables are expertly designed and constructed of top quality materials to deliver dependable high-definition performance, and are backed by Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Quick-connect single HDMI cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.
- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI with Ethernet)

Features

- **HIGH SPEED HDMI CABLE:** 6ft (1.8m) HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** Ultra HD high speed fully molded 4K HDMI cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** This HDMI to HDMI cable has a 28AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid (85% coverage) improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 6 ft (1.8 m) Black HDMI 1.4b HDMI Cord Male to Male 28 AWG Gold-plated connectors PVC Jacket Shield: Al-Mylar foil w/ 85% Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.3 in [7.3 mm]
Product Length	6.0 ft [1.8 m]
Product Width	0.8 in [20.2 mm]
Product Height	0.4 in [10.3 mm]
Weight of Product	5.2 oz [148.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	5.5 oz [156.0 g]

What's in the Box

Included in Package	6 ft High Speed HDMI Cable with Ethernet - HDMI - M/M
---------------------	---

**Product appearance and specifications are subject to change without notice.*

