



## Shielded Cat6A Keystone Jack – 6-Pack

TC-K06C6A (v1.0R)

- 6-pack of Cat6A tool-less keystone jacks
- 180° angle termination design
- Cat6A for steady connection to copper Gigabit & 10G switches
- Compatible with Cat5e, Cat6 and Cat6A cabling
- Color-coded labeling for T568A and T568B wiring schemes
- Gold-plated contacts for improve conductivity and corrosion resistance
- Use with TC-KP24S shielded blank keystone patch panel (sold separately)

TRENDnet's Shielded Cat6A Keystone Jack – 6-Pack, model TC-K06C6A includes six Cat6A shielded keystone jacks for use with TRENDnet's TC-KP24S blank shielded keystone patch panel. These metal keystone jacks are designed for gigabit and 10G copper Ethernet network applications. Each shielded keystone jack is designed for use with Cat6A shielded cabling, which eliminates EMI and crosstalk ensuring peak performance and data integrity. These shielded Cat6A keystone jacks feature a convenient tool-less design with T568A and T568B color-coded labeling for easy cable termination.



### Shielded Design

Shielded metal housing design protects against EMI/RFI noise for a more stable connection



### Cat6A Performance

Each shielded Cat6A keystone jack provides up to 10Gbps speeds over 100m (328 ft.) of Cat6A Ethernet cabling.



### Tool-less Design

Tool-less design with convenient wire separation for easy installation.



### Convenient Color-Coding

Color-coded labeling for T568A and T568B wiring schemes



### 6-Pack

Includes six Cat6A keystone jacks for use with TRENDnet's TC-KP24S blank shielded keystone patch panel



### Compatibility

Works with blank shielded keystone patch panels and wall plates



### Metal Construction

Each keystone jack features an all metal design for long lasting durability

## Specifications

<b>Features</b>	<ul style="list-style-type: none"> <li>• 6-pack of Cat6A tool-less keystone jacks</li> <li>• 180° angle termination design</li> <li>• Cat6A for steady connection to copper Gigabit &amp; 10G switches</li> <li>• Color-coded labeling for T568A and T568B wiring schemes</li> <li>• Gold-plated contacts for improve conductivity and corrosion resistance</li> <li>• Use with TC-KP24S shielded blank keystone patch panel (sold separately)</li> </ul>
<b>Dimensions</b>	• 38 x 22 x 17mm (1.5 x 0.87 x 0.67 in.)
<b>Weight</b>	• 26g (0.92 oz.)
<b>Warranty</b>	• 2 year

### PACKAGE CONTENTS

- TC-K06C6A x 6
- Cable ties x 6
- Quick Installation Guide

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.