

36U Adjustable 4 Post Server Equipment Open Frame Rack Cabinet

Product ID: 4POSTRACK36



The 4POSTRACK36 Adjustable Depth 36U 4-Post Rack provides a durable, open frame housing for rackmount servers and networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The equipment cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation.

The 36U rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For added versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed on the bottom of the 36U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

StarTech.com also offers the following Open Frame 4-Post Rack/Cabinets:

- [12U Open 4 Post Rack/Cabinet](#)
- [25U Open 4 Post Rack/Cabinet](#)
- [42U Open 4 Post Rack/Cabinet](#)

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rack mount equipment where security at the rack level is not required
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Adjustable depth mounting rails ensure broad equipment compatibility
- Heavy-duty, pre-drilled base lets you bolt the server rack to the floor when mounting heavy rackmount equipment
- TAA compliant for GSA Schedule purchases
- Heavy gauge mounting rails
- Unobstructed ventilation
- Optional caster kit available

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	C-Shape
	Rack Type	4-Post
	Special Features	Adjustable Mounting Rails
		Base Plate with Floor-Anchoring Holes
		Casters (Optional)
U Height	36U	
Wallmountable	No	
Performance	Weight Capacity	1000 lb [452.5 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Maximum Mounting Depth	39.2 in [99.5 cm]
	Minimum Mounting Depth	18.3 in [46.6 cm]
	Product Height	67.5 in [171.5 cm]
	Product Height with Casters	70.3 in [178.6 cm]
	Product Length	23.7 in [60.1 cm]
	Product Width	22.6 in [57.3 cm]
	Weight of Product	96.2 lb [43.5 kg]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Package Height	6.7 in [16.9 cm]
	Package Length	5.9 ft [1.8 m]
	Package Width	25.3 in [64.2 cm]
	Shipping (Package) Weight	104.3 lb [47.2 kg]
What's in the Box	Included in Package	1 - 36 U Open Rack
		1 - Assembly Kit (Screw, wrench, caps)
		62 - M5 Screws

62 - M5 Cage Nuts

1 - Assembly Instructions

Product appearance and specifications are subject to change without notice.