

### 3 ft eSATA and USB A to Power eSATA Cable - M/M

StarTech ID: ESATAUSBMM3



This eSATA and USB A Male to Power eSATA Cable provides a 3ft connection between an external drive enclosure equipped with a power eSATA port and the eSATA and USB port on a PC/Notebook, providing both power (through USB) and data (through SATA) using a single cable.

Expertly designed and constructed of only top quality materials, the 3ft eSATA and USB A Male to Power eSATA Male cable is backed by StarTech.com's Lifetime Warranty.

### Applications and Solutions

- Connect your Powered eSATA device to your PC or Notebook even if you do not have a Powered eSATA port

## Features

- Combo eSATA + USB connection

## Technical Specifications

- Color: Black
- Carton Quantity: 150
- Shipping (Package) Weight: 0.19 lb [0.09 kg]
- Cable Length: 3 ft [0.91 m]
- Cable Jacket Type: PVC - Polyvinyl Chloride
- Connector A: 1 - 11 pin Power eSATA (eSATA/USB, 5V) Male
- Connector B: 1 - ESATA Data 7 Pin Male
- Connector B: 1 - USB A Male
- Storage Temperature: -20&deg;C to 60&deg;C (-4&deg;F to 140&deg;F)
- Operating Temperature: -20&deg;C to 50&deg;C (-4&deg;F to 122&deg;F)
- Humidity: 60~75% RH