

1:7 Standalone USB Duplicator and Eraser - for USB Flash Drives

Product ID: USBDUPE17



This USB duplicator and eraser lets you clone or erase up to seven USB flash drives, without a host computer connection. This means you can work more efficiently and manage larger batches of USB drives, saving time and effort.

The standalone USB duplicator and eraser is perfect for IT professionals and system administrators in corporate, education, marketing, or sales environments.

Efficient 1:7 drive duplication

The duplicator lets you copy up to seven drives simultaneously, and offers both synchronous and asynchronous duplication, with speeds up to 1.5GB per minute. The asynchronous feature means you can remove and replace USB storage devices while other copies continue to run. The eraser/duplicator offers two modes of duplication: system and file and whole file.

Erase multiple USB drives simultaneously

The drive duplicator/eraser lets you erase up to seven flash drives at the same time, so it's easy to clean large batches of USB drives for reuse. The flash drive duplicator features three modes of erasing: quick erase, single pass erase, and multi-pass erase (meets DoD standards).

Designed for ease of use

The flash drive duplicator and eraser supports USB 3.0, USB 2.0 and USB 1.1 flash drives, providing an easy and cost-effective way to re-use and re-purpose your USB drives. It features a robust metal housing and a compact, standalone design that makes it the perfect desktop companion. The duplicator/eraser also has an LCD display that makes it easy to monitor erasing and duplication to ensure completion.

The USBDUPE17 is TAA compliant and backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Software and operating system update rollouts
- Marketing collateral copying and distribution
- Backup USB flash drives without a host computer
- Clean and prepare USB drives for reuse
- Testing and evaluating USB drives
- Professionals who require identical backups for when data integrity is crucial, such as data recovery
- IT administrators who wish to erase multiple drives simultaneously in preparation for use in other applications

Features

- Duplicate or erase up to seven USB 3.0, USB 2.0 and USB 1.1 flash drives, without connecting to a host computer
- 1:7 standalone duplication with two duplication modes: system and file, and whole file
- Erase up to seven drives at the same time, with three modes: quick erase, single pass erase, and multi-pass erase (meets DoD standards)
- TAA compliant
- Compact metal design
- Built-in LCD display
- Duplication speeds up to 1.5GB per minute
- Includes universal power adapter
- Supports both asynchronous and synchronous copy modes, for quick batch swapping with 64 MB of internal memory

Hardware

Warranty	2 Years
Bus Type	USB 2.0
Number of Drives	7
Compatible Drive Types	USB Flash Drive

Drive Installation	Removable
Chipset ID	Xilinx - Spartan (XC3S700A)
Buffer Size	128 MB

Performance

Duplication Modes	System and File
	Sector by Sector (Whole Drive)
Erase Modes	Quick Erase
	1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear)
	3-Pass Overwrite
Duplication Speed	1.5GBpm
Max Drive Capacity	3TB
Insertion Rating	1500 times
MTBF	176,549 hours

Connector(s)

Drive Connectors	USB Type-A (4 pin) USB 2.0
------------------	----------------------------

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

System and Cable Requirements	<p>For duplication, the destination drives must be of equal or greater capacity than the source drive.</p> <p>Supports copying/cloning/erasing to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure (sold separately) if supported by the storage media</p>
-------------------------------	--

Indicators

LED Indicators	Green (Activity/Successful Copy)
	Red (Error)



Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.6A Max
Output Voltage	12V DC
Output Current	9A
Plug Type	4-pin DIN
Power Consumption (In Watts)	108W

Environmental

Operating Temperature	5C ~ 45C (41F ~ 113F)
Storage Temperature	-20C ~85C (-4F ~ 185F)
Humidity	20% ~ 80%

Physical Characteristics

Color	Black
Material	Steel
Product Length	7.5 in [19 cm]
Product Width	6.3 in [16 cm]
Product Height	1.4 in [34.6 mm]
Weight of Product	2.3 lb [1.0 kg]

Packaging Information

Package Length	17.5 in [44.5 cm]
Package Width	9.3 in [23.5 cm]
Package Height	3.3 in [85 mm]
Shipping (Package) Weight	6.5 lb [3.0 kg]

What's in the



Box

Included in Package	duplicator and eraser
	universal power adapter (NA/JP, UK, EU, ANZ)
	instruction manual

****Product appearance and specifications are subject to change without notice.***

