

## 6in DisplayPort to Mini DisplayPort Video Cable Adapter - M/F

**Product ID:** DP2MDPMF6IN



The DP2MDPMF6IN DisplayPort to Mini DisplayPort Adapter turns a mini DisplayPort (male) connector into a regular DisplayPort (male) connector, making it easy to connect a mini DisplayPort-equipped monitor to a laptop that only provides a standard DisplayPort output (e.g. Apple, Toshiba etc.).

This 6in DisplayPort to Mini DisplayPort Video Cable Adapter is designed & manufactured to DisplayPort v1.2 standards; Max resolution: 2560x1600 60Hz (depends on the cable quality; Attached cable must be at least DP 1.2).

### Certifications, Reports and Compatibility

### Applications

- Allows mini DisplayPort monitors, such as Apple Cinema Displays to be connected to computers equipped with standard DisplayPort connections

### Features

- Designed and manufactured to DisplayPort version 1.2 standards; Max resolution: 2560x1600 60Hz (subject to the quality of the cable; Attached cable must be at least DP1.2)
- Molded latching connectors with strain relief

---

#### Hardware

Warranty	Lifetime
Number of Conductors	19

Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)

---

#### Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	Mini-DisplayPort (20 pin)

---

#### Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

---

#### Physical Characteristics

Color	Black
Wire Gauge	32 AWG
Max Connector Dimension	0.8 in [20 mm]
Cable Length	6.0 in [15.2 cm]
Cable OD	0.2 in [4.7 mm]
Product Length	5.9 in [15.0 cm]
Product Width	0.8 in [19.9 mm]
Product Height	0.5 in [13.6 mm]
Weight of Product	0.5 oz [14.0 g]

---

#### Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package)	0.8 oz [22.0 g]



Weight

---

**What's in the  
Box**

Included in Package	6in DisplayPort to Mini DisplayPort Video Cable - M/F
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

