

3ft USB to RS232 DB9 Serial Adapter Cable - M/M

Product ID: ICUSB232SM3



The ICUSB232SM3 3ft USB to Serial Adapter Cable lets you connect DB9 RS232 serial devices to your Mac or PC laptop or desktop computer through an available USB port, as though the computer offered an onboard DB9M connector.

Unlike typical USB to serial converter cables where the conversion takes place at the DB9 end, the StarTech.com ICUSB232SM3 features a converter chip on the USB end. Converting at the USB source overcomes the 15ft. technical limit of USB cables, allowing for a much greater serial DB-9 extension cable (50ft.+ is possible depending on the application) if necessary.

Simple to install and use, this USB to Serial adapter is a cost-effective solution that bridges the compatibility gap between modern computers and legacy serial peripherals.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync



Features

- Supports serial data transfer rates of up to 1 Mbps
- No external power needed draws power from the USB connection
- Compatible with modems, printers, bar code scanners, servers, PDUs, and nearly any serial RS232 equipment
- Thin,lightweight design
- Easy to setup and install

Hardware		
	Warranty	Lifetime
	Ports	1
	Interface	Serial
	Bus Type	USB 2.0
	Port Style	Cable Adapters
	Industry Standards	RS232, USB 1.1/2.0
	Chipset ID	Prolific - PL2303HXD
Performance		
	Serial Protocol	RS-232
	Max Baud Rate	921.6 Kbps
	FIFO	192 Bytes
Connector(s)		
	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	DB-9 (9 pin, D-Sub)
Software		
	OS Compatibility	Windows CE 4.2, 5.2, 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10
		Windows Server 2003, 2008 R2, 2012, 2016, 2019
		macOS 10.6 to 10.15, 11.0
		Linux 2.4.x to 4.11.x <i>LTS Versions only</i>

Environmental



Operating Temperature 0C to 60C (32F to 140F)

Storage Temperature -20C to 80C (-4F to 176F)

Humidity 0~65% RH

Physical Characteristics

Color Black

Material Plastic

Cable Length 36.0 in [91.4 cm]

Product Length 36.0 in [91.4 cm]

Product Width 1.4 in [35.0 mm]

Product Height 0.6 in [15.0 mm]

Weight of Product 2.0 oz [56.0 g]

Packaging Information

Package Length 8.7 in [22.0 cm]

Package Width 7.9 in [20.0 cm]

Package Height 0.6 in [15.0 mm]

Shipping (Package)

Weight

2.5 oz [70.0 g]

What's in the Box

Included in Package USB to Serial Converter

Cable Nuts

^{*}Product appearance and specifications are subject to change without notice.