

## Vented Blank Panel with Hinge for Server Racks - 4U

**Product ID:** RKP NLHV4U



You can improve the appearance and airflow of any standard 19-inch server rack, while still enjoying easy access to unused space, using this hinged 4U blanking panel. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The blanking panel creates a clean and professional look by covering empty space and visible cables. Adding blanking panels to your server racks offers a tidier appearance for a more organized server room.

The blanking panel features a vented design which enables unobstructed airflow through your rack. The panel helps to maximize airflow to ensure your equipment is running at an optimal temperature.

This solid rack-panel features a hinged design that enables you to open the panel for fast and easy server access. You can quickly open the panel, make your required adjustments, and when you're finished, simply close the panel to restore the professional appearance and order of your server room. This rack panel is reversible enabling you can install it on the left or the right side of your rack, for a versatile installation. This rack panel also comes complete with rack installation screws and nuts, giving you everything you need to ensure a hassle-free installation.

The RKP NLHV4U is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Fill in unused gaps between equipment in server racks and cabinets
- Access your covered rack with an open-and-shut design
- Increase the airflow in your server rack with vented design that helps keep your equipment running at an optimal temperature

## Features

- Create a tidy and professional look by covering unused rack space
- Easily access rack components by opening the hinged panel
- TAA compliant for GSA Schedule purchases
- Versatile installation options with a reversible blank panel that can open from the left or the right side
- 4U panel that mounts to any standard 19 in. 2 or 4-post racks
- Sturdy steel construction
- Rack screws and nuts included

---

### Hardware

Warranty	2 Years
U Height	4U
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front Only)

---

### Physical Characteristics

Color	Black
Material	Steel
Product Length	19.0 in [48.3 cm]
Product Width	7.0 in [17.7 cm]
Product Height	0.6 in [15 mm]
Weight of Product	20.7 oz [585 g]

---

### Packaging Information

Package Length	20.9 in [53.1 cm]
Package Width	7.9 in [20 cm]
Package Height	1.8 in [45 mm]



Shipping (Package) Weight	27.4 oz [777 g]
------------------------------	-----------------

---

**What's in the  
Box**

Included in Package	4U Hinged Vented Rack Panel
	5/8" #10-32 UNF Screws
	#10-32 UNF Cage Nuts

---

***\*Product appearance and specifications are subject to change without notice.***

