

Data Sheet

MSA Uncoded SFP+ Module - 10GBASE-SR - 10GbE Multi Mode Fiber (MMF) Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 300m - 850nm - DDM

Product ID: SFP-10GBASE-SR-ST



The SFP-10GBASE-SR-STS is an 10 GMSA compliant fiber SFP+ transceiver that's designed, programmed and tested to work with 10GBase-SR compatible MSA switches and routers. The SFP+ transceiver module supports a maximum distance of up to 300 m (984 ft) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 850nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 300 m (984 ft)
- MTBF: 646,156,559 hours
- **Power Consumption:** < 1.3 W
- Digital Diagnostics Monitoring (DDM): Yes

www.startech.com 1 800 265 1844



Data Sheet

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP+ modules and direct-attach SFP+ cables, providing the convenience and reliability you need to ensure dependable network performance.

www.startech.com 1 800 265 1844



Certifications, Reports and Compatibility

StarTechcom

Hard-to-find made easy*









- 100% MSA UNCODED SFP+ TRANSCEIVER: Designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver dependable 10GbE connectivity
- TECHNICAL SPECS: 10GBASE-SR | 10Gbps | Multi Mode (MMF) | LC Connector | 850nm | Digital Diagnostic Monitoring (DDM) | Distances up to 300m (984ft)
- TESTED FOR COMPATIBILITY: Hot-swappable in MSA Compliant routers and switches; DDM support reports the transceiver's status to most SNMP network management tools.
- LIFETIME WARRANTY: Backed by a lifetime warranty on the life of the module itself and not the life of your switch; our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- WORKS WITH MSA COMPLIANT SWITCHES: Works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

StarTechcom

Hard-to-find made easy*

Data Sheet

	Warranty	Lifetime
Hardware	Compatible Brand	MSA Compliant
Performance	DDM	Yes
	Maximum Data Transfer Rate	10.00 Gbps
	Power Consumption (In Watts)	< 1.3W
Physical Characteristics	Product Height	13.700
	Product Length	0.5 in [1.4 cm]
	Product Width	58.400
	Weight of Product	20.000
Packaging Information	Package Height	31.000
	Package Length	115.000
	Package Width	90.000
	Shipping (Package) Weight	50.000
What's in the Box	Included in Package	1 - SFP+ Transceiver

Product appearance and specifications are subject to change without notice.

www.startech.com 1 800 265 1844