

30 ft DVI-D Single Link Cable - M/M

Product ID: DVIDSMM30



The DVIDSMM30 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and offers 30 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 30ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (19 pin)
Connector B	DVI-D (19 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	30.0 ft [9.1 m]
Product Length	30.0 ft [9.1 m]
Weight of Product	23.1 oz [655 g]

Packaging Information

Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.8 in [45 mm]
Shipping (Package) Weight	23.7 oz [672 g]

What's in the Box

Included in Package	30ft DVI-D Single Link Cable - M/M
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***

