

8in Nylon Cable Ties - Pkg of 1000

Product ID: CV200K



Our 8in Cable Ties feature durable yet pliable UL-approved Nylon construction.

Certifications, Reports and Compatibility

Applications

Features

Performance

Warranty	2 Years
Minimum Tensile Strength	39.8 lb [18 kg]

Physical Characteristics

Materials	UL-approved Nylon 66, 94V-2
Diameter	Max. Bundle - 2.17 in[55 mm]
Product Length	8.0 in [20.3 cm]
Product Width	0.1 in [3.6 mm]

Product Height	0.0 in [0.0 mm]
Weight of Product	30.5 oz [865.0 g]

Packaging Information

Package Quantity	1000
Package Length	13.0 in [33.0 cm]
Package Width	10.0 in [25.5 cm]
Package Height	2.4 in [60.0 mm]
Shipping (Package) Weight	31.1 oz [882.0 g]

What's in the Box

Included in Package	8 inch Nylon Cable Ties
---------------------	-------------------------

****Product appearance and specifications are subject to change without notice.***

