

## Ceiling TV Mount - 1.8' to 3' Short Pole

**Product ID:** FPCEILPTBSP



This ceiling TV mount supports VESA mount compatible TVs from 32" to 75" in size, with a weight capacity of up to 110 lb. (50 kg). It lets you save wall and floor space by hanging your flat-panel LCD, LED or plasma TV from the ceiling in a prominent area.

The ceiling mount is ideal for use in corporate boardrooms, lobbies, entrances, restaurants, bars and meeting places.

With a telescopic pole, the TV mount lets you suspend a display at your desired distance from the ceiling. This works well with a range of ceiling heights. The steel pole can extend from 22" to 33.5" (560 to 910 mm), with a total lift (height extension) of 13.7" (350 mm).

The flat-screen ceiling mount accommodates a wide variety of ceiling types. You can swivel the TV to work with virtually any type of ceiling for level viewing, including sloped ceilings (up to 60 degrees), and pitched or horizontal (flat) ceilings.

You can adjust your TV to create a comfortable viewing angle, by tilting it up to -25 degrees down towards your audience for optimum visibility. Plus, the full-motion mount lets you swivel your display around the pole + 180 / - 180 degrees, without using tools.

Simply attach the included vertical brackets, with built-in hooks, to the back of your TV. Once attached, hang your TV securely onto the ceiling mount. The +/-3 degree post-installation leveling adjustments ensure ideal positioning after hanging.

FPCEILPTBSP is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

- Suspend a flat-screen TV from the ceiling for easy viewing
- Ideal for boardrooms, lobbies, entrances, meeting spaces, classrooms
- Keep your guests informed and entertained

## Features

- Save space by suspending your 32 to 75" flat-screen TV from the ceiling; Supports TVs up to 110lb (50 kg)
- Min-max pole length extension of 22.0" to 35.8" (560 to 910 mm)
- Ceiling TV mount swivels +60 /-60 degrees to adjust to sloped or level ceilings
- Full-motion mount lets you swivel the display +180 /-180 degrees around the pole and tilt downwards -25 degrees, without using tools
- Easy setup, with a hook-and-mount design
- Universal hanging TV ceiling mount supports LG, Samsung, Sony, and Sharp TVs among others (screws/spacers incl) & VESA hole patterns of 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400

---

## Hardware

|                         |               |
|-------------------------|---------------|
| Warranty                | 5 Years       |
| Wallmountable           | No            |
| Cable Management        | Yes           |
| # of Displays Supported | 1             |
| Mounting Options        | Ceiling Mount |
| VESA Hole Pattern(s)    | 200x200 mm    |
|                         | 200x400 mm    |
|                         | 200x300 mm    |
|                         | 300x200 mm    |
|                         | 300x300 mm    |
|                         | 400x200 mm    |
|                         | 400x300 mm    |
|                         | 400x400 mm    |

|                            |                  |
|----------------------------|------------------|
|                            | 600X200 mm       |
|                            | 600x300 mm       |
|                            | 600x400 mm       |
| Mounting Surface Thickness | 560 mm to 910 mm |

---

## Performance

|                               |   |
|-------------------------------|---|
| General Specifications        | Post-Installation Leveling Adjustment: +/-3 |
| Weight Capacity (Per Display) | 110.5 lb [50 kg]                            |
| Minimum Display Size          | 32in  |
| Maximum Display Size          | 75"   |
| Video Wall                    | No  |
| Fits Curved Display           | Yes   |
| Height Adjustment             | Yes   |
| Minimum Height                | 22.0 in [56 cm]                             |
| Maximum Height                | 35.8 in [91 cm]                             |
| Display Tilt                  | +0 / -25                                    |
| Swivel / Pivot                | +180 to -180                                |
| Display Rotation              | 360   |
| Anti-theft                    | No  |

---

## Physical Characteristics

|                |                   |
|----------------|-------------------|
| Color          | Black             |
| Material       | Steel             |
| Product Length | 17.1 in [43.5 cm] |
| Product Width  | 26.8 in [68 cm]   |
| Product Height | 3.8 ft [1.2 m]    |



|                   |                  |
|-------------------|------------------|
| Weight of Product | 10.8 lb [4.9 kg] |
|-------------------|------------------|

---

**Packaging Information**

|                           |                   |
|---------------------------|-------------------|
| Package Length            | 14.4 in [36.6 cm] |
| Package Width             | 30.4 in [77.1 cm] |
| Package Height            | 5.9 in [14.9 cm]  |
| Shipping (Package) Weight | 15.1 lb [6.8 kg]  |

---

**What's in the Box**

|                     |                        |
|---------------------|------------------------|
| Included in Package | ceiling mount and pole |
|                     | extension pole         |
|                     | vertical brackets      |
|                     | horizontal bracket     |
|                     | bolts                  |
|                     | nuts                   |
|                     | wrench                 |
|                     | hex key                |
|                     | mounting template      |
|                     | M5x14 mm screws        |
|                     | M6x14 mm screws        |
|                     | M6x30 mm screws        |
|                     | M8x30 mm screws        |
|                     | M8x50 mm screws        |
|                     | rectangular washers    |
|                     | small spacers          |
|                     | large spacers          |
|                     | 6.3x55 mm screws       |



concrete anchor

circular washers

instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

