

Multiple Video Input with Audio to HDMI Switcher - HDMI / VGA / Component

Product ID: VS721MULTI



The VS721MULTI Multiple Video Input to HDMI Switcher enables users to switch between 7 different audio-video sources to a single HDMI-equipped display.

This versatile switcher is the perfect solution for combining digital and analog video sources (RGB/YpPr/YCbCr) with your digital HDMI display, eliminating the cost of upgrading individual components (i.e. DVD player, PC, VCR, etc.).

An all-in-one multimedia solution, the video converter/switcher includes support for full high definition 1080p video resolution as well as digital and analog audio. Plus, the switch features RS232 remote serial control, and includes a convenient IR remote control for switching between video sources .

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Convert analog and digital video to HDMI for a variety of applications such as switching between consumer electronics devices (e.g. Blu-ray Disc players, satellite receivers, video game consoles and other devices)

Features

- Supports analog PC Resolution input and output up to WUXGA (1920x1200) @ 60Hz
- HDMI and HDCP compliant
- Supports analog HDTV RGB/YpPr/YCbCr input, output up to 1080p @ 60Hz

Hardware

Warranty	2 Years
AV Input	HDMI S-Video Composite VGA Component
Ports	7
AV Output	HDMI
Cabling	HDMI
Audio	Yes
Industry Standards	High Speed HDMI, HDCP

Performance

Maximum Analog Resolutions	VGA: 1920x1200, YPbPr: 1920x1080
Maximum Digital Resolutions	1920x1200
Supported Resolutions	Support VGA mode, 640x480, 720x400, 800x600, 848x480, 1024x768, 1152x864, 1280x720, 1280x768, 1280x800, 1280x960, 1280x1024, 1360x768, 1400x1050, 1440x900, 1440x1050, 1600x1200, 1680x1050, 1920x1080, 1920x1200 Support YPbPR mode, 720x480, 720x576, 720x480, 720x576, 1280x720, 1920x1080, 1920x1080
Wide Screen Supported	Yes

Connector(s)

Connector A	HDMI (19 pin) VGA (15 pin, High Density D-Sub) Component Video (3 x RCA)
-------------	--



S-Video (4 pin, Mini-DIN)
Composite Video (1 x RCA)
RCA
3.5 mm Mini-Jack (3 Position)

Connector B HDMI (19 pin)

Software

OS Compatibility Windows 10 (32/64), 8/8.1 (32/64), 7 (32/64), Vista(32/64), XP(32/64), 2000
Windows Server 2008 R2, 2003(32/64)

Indicators

LED Indicators

- 1 - HDMI
- 2 - HDMI
- 3 - HDMI
- 4 - VGA
- 5 - YPbPr
- 6 - CVSB
- 7 - S-VIDEO

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 0.6 A

Output Voltage 12V DC

Output Current 1.5 A

Center Tip Polarity Positive

Plug Type M

Power Consumption (In Watts) 18



Environmental

Operating Temperature	0c to 70c (32F to 158F)
Storage Temperature	-20c to 85c (-4F to 185F)
Humidity	0% to 95% RH Non-Condensing

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	15.1 in [38.4 cm]
Product Width	6.8 in [17.3 cm]
Product Height	1.8 in [45.0 mm]
Weight of Product	4.0 lb [1.8 kg]

Packaging Information

Package Length	18.1 in [45.9 cm]
Package Width	10.2 in [26.0 cm]
Package Height	3.5 in [90.0 mm]
Shipping (Package) Weight	6.0 lb [2.7 kg]

What's in the Box

Included in Package	multiple format to HDMI audio video switch
	IR remote control
	mounting kit
	RS232 serial cable (6 ft.)
	RS-232 control software CD
	universal power adapter (NA, EU, UK, AU)
	instruction manual

****Product appearance and specifications are subject to change without notice.***

