

2 Port Professional USB KVM Switch Kit with Cables

Product ID: SV231USB



The SV231SUB 2 Port Professional USB KVM Switch Kit with Cables offers simple control of two Mac or PC computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The 2 Port KVM switch includes 2 USB KVM cables, providing a complete out-of-the-box KVM solution saving you time and money. An integrated 3 port USB hub allows you to share connected USB peripherals between connected computers as though they were connected directly. A compact form factor design and rear-port connections to master and slave computers minimizes disruption to your workspace.

A cross-platform solution, this OS independent KVM switch supports high resolution applications up to 1920x1440, and provides a smooth operating experience when controlling mixed (Windows/Mac/Linux) environments.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Dual system control for a single workstations increasing user productivity in the office
- Provide centralized control for multiple high-res Digital Signage server control
- Great for manufacturing line computer control, simplifying access to multiple systems
- Perfect for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice

Features

- Control 2 computers from one USB keyboard/mouse/monitor
- Share 3 different USB peripherals using the integrated hub
- High 1920x1440 resolution capability
- Front panel push buttons for easy computer selection
- OS independent - No software or drivers required
- Supports keyboard and mouse plug and play
- Selectable auto scan time interval
- Supports DDC2B VGA monitors
- USB self-power operation

Hardware

Warranty	3 Years
U Height	1U
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
DVI Support	No
IP Control	No
Hot-Key Selection	No
Maximum Cable Length	15.0 ft [4.6 m]



Maximum Analog Resolutions	1920 x 1440
Auto Scan	3, 8, 15 & 30 seconds
Maximum Number of Users	1
Port Selection Support	Push Button
MTBF	111,000 Hours

Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0
Host Connectors	VGA (15 pin, High Density D-Sub) USB B (4 pin)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	This KVM supports the use of VGA cables up to 100ft in length - active extension required for USB to achieve that distance
------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N N
Power Consumption (In Watts)	10



Physical Characteristics

Color	Black
Material	Steel
Cable Length	6.0 ft [1.8 m]
Product Length	4.9 in [12.4 cm]
Product Width	2.8 in [70 mm]
Product Height	1.6 in [40 mm]
Weight of Product	14.9 oz [421 g]

Packaging Information

Package Length	9.4 in [23.8 cm]
Package Width	7.4 in [18.7 cm]
Package Height	3.6 in [92 mm]
Shipping (Package) Weight	2.5 lb [1.1 kg]

What's in the Box

Included in Package	2 Port USB KVM Switch
	2 IN 1 USB/VGA Cables
	Power Adapter
	Manual

****Product appearance and specifications are subject to change without notice.***

