

Dual-Monitor USB 3.0 Docking Station with DVI and Vertical Stand

Product ID: USB3SDOCKDD



This dual-monitor USB 3.0 docking station turns your laptop into a dual-monitor workstation with flexible setup options.

The dual-DVI docking station adds dual-monitor support to your workstation, with resolution support up to 2048x1152. With more screen space, you can simultaneously access multiple applications and reference material on one display while composing on the other. To ensure the USB 3.0 dock supports a variety of displays, two display adapters (DVI to VGA and DVI to HDMI) are included.

Transform your laptop into a workstation that supports all of your peripherals. This docking station features five USB 3.0 (USB 3.1 Gen 1) ports. The two front-facing USB ports are USB fast-charge ports (USB Battery Charging Specification 1.2). These accessible ports charge your mobile devices faster than standard USB ports, with or without your laptop connected to the dock. The dock also has a GbE port, headset jack and separate 3.5 mm audio and mic ports, so you'll have all the connections you need.

You can free up valuable desk space by positioning the dock vertically on your work surface using the included (optional) stand.

The USB3SDOCKDD is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Use dual displays to work on multiple documents simultaneously in office applications
- View multiple monitors at a glance, in financial or investment firms
- Create a quick-connect workstation that supports your existing HDMI, VGA, and DVI monitors



Features

- Dock your USB 3.0 equipped Mac or Windows laptop with support for several dual monitor configurations using the included video adapters
- Connect and charge your USB devices with 5x USB 3.0 ports, including two Fast-Charge USB ports
- Save space on your desktop by placing the dock in a vertical orientation with the included dock stand

• Add wired network connectivity and audio devices with the Gigabit Ethernet RJ-45 port and headset jack.

Hardware

Warranty 3 Years

4K Support No

Fast-Charge Port(s) Yes

Displays Supported 2

Bus Type USB 3.0

Industry Standards IEEE 802.3, IEEE 802.3u, IEEE 802.3ab

USB Battery Charging Specification Rev. 1.2

USB 3.0 - Hub ports support USB 2.0/1.1 backward-compatibility

Chipset ID DisplayLink - DL-3900

Genesys Logic - GL3520, VIA/VLI - VL817

Performance

Maximum Data Transfer 5 Gbps (USB 3.0)

Rate

2 Gbps (Ethernet; Full-Duplex)

Maximum Analog

Resolutions

2048x1152 (VGA)

Maximum Digital Resolutions

2048x1152 (Dual-Link DVI/HDMI)

Lower resolutions are also supported.

Type and Rate USB 3.0 - 5 Gbit/s

UASP Support Yes

Compatible Networks 10/100/1000 Mbps



	Auto MDIX	Yes
	Full Duplex Support	Yes
Connector(s)		
	Connector Type(s)	DVI-D (25 pin)
		DVI-I (29 pin)
		USB 3.0 A (Fast-Charge, 9 pin)
		USB Type-A (9 pin) USB 3.0 (5 Gbps)
		RJ-45
		3.5 mm Mini-Jack (4 Position)
		USB Type-B (9 pin) USB 3.0
Software	000 411111	Min I VP OPO (oo I ii) Vii I T O O I I O
	OS Compatibility	Windows XP SP3 (32-bit), Vista, 7, 8, 8.1, 10
		macOS 10.6 - 10.12, 10.14 - 10.15, 11.0 Chrome OS v55+
		Official GG VSST
Special Notes / Requirements		
	System and Cable Requirements	USB 3.0 port interface and USB 3.0 cable to connect the Laptop Docking Station to a host computer (USB 3.0 host cable included)
	Note	HDMI and VGA adapters included
		VGA adapter can only be used on the DVI-I (29-pin) port
		The DVI-I connector supports DVI-I signaling (digital and analog)
		This USB docking station is not intended for graphical intensive applications, such as gaming
Indicators		
	LED Indicators	Power
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.8 A



Output Voltage 12V DC

Output Current 2 A

Center Tip Polarity Positive

Plug Type H

Power Consumption (In

Watts)

Environmental

Operating Temperature 0C to 50C (32F to 122F)

24W

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 5~85% RH

Physical Characteristics

Color Black & Silver

Material Aluminum and Plastic

Cable Length 39.4 in [100 cm]

Product Length 3.3 in [83.0 mm]

Product Width 0.9 in [23.0 mm]

Product Height 7.0 in [17.8 cm]

Weight of Product 10.1 oz [285.0 g]

Packaging Information

Package Length 7.3 in [18.6 cm]

Package Width 10.0 in [25.5 cm]

Package Height 3.7 in [95.0 mm]

Shipping (Package)

Weight

2.2 lb [1.0 kg]

What's in the Box

Included in Package USB 3.0 Laptop Docking Station



1m USB 3.0 Cable			
Rubber Feet			
Stand			
Stand Screws			
Screwdriver			
DVI to VGA Adapter			
DVI to HDMI Adapter			
Universal Power Adapter (NA/JP, EU, UK, ANZ)			
Driver CD			

Instruction Manual

^{*}Product appearance and specifications are subject to change without notice.