

Desk-mount Dual-Monitor Arm - Cross Bar - Grommet/Desk Clamp Mount

Product ID: ARMBARDUOG



This deskmount dual-monitor arm lets you mount two 13" to 27" VESA mount monitors, each weighing up to 17.6 lb. (8 kg), onto a single low-profile base. It gives you flexible desk-clamp or grommet-hole mounting, letting you save space while creating an ergonomic workspace in any office environment.

With a stable dual-arm design, the double-monitor mount lets you create more usable work space by mounting your monitors side by side on a single base. The screen mount features a flat low-profile back that lets you position your displays against a wall or cubicle wall.

The computer monitor desk mount features adjustable height along the pole. The smooth +/- 30 tilt motion and +/- 30 swivel make it easy to find the optimal viewing angle. You can also rotate your display 360 for portrait or landscape viewing, and make sure your displays are perfectly aligned using the micro-adjustment knob.

The dual-monitor arm is easy to install, with the desk-clamp or grommet mount (hardware included). Integrated cable management keeps your workspace organized. It works well with most desks, including sit-stand workstations.

Adding two monitors gives you the extra screen space you need to simplify multitasking and maximize your productivity.

ARMBARDUOG is backed by a 5-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount two monitors on a single base to save desk space
- Maximize office space, creating a dual-monitor workstation against a wall or cubicle wall

- Works with sit-stand workstations, using the desk clamp or grommet mount

Features

- Save space by mounting two monitors up to 27" onto a single base (max. weight 17.6 lb. / 8 kg)
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 23"/58.4 cm)
- Work comfortably with adjustable height, +/- 30tilt, +/- 30swivel and 360 rotation
- Versatile use with desk-clamp or grommet-hole mounting
- Place monitors close to a wall/cubicle wall, with a low-profile design

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Articulating	No
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

Performance

General Specifications	Pole Height: 14.2" (360 mm) Dual-Arm Span: 32.87" (835 mm)
Weight Capacity (Per Display)	17.7 lb [8 kg]
Minimum Display Size	13"
Maximum Display Size	27in

Height Adjustment	Yes
Maximum Height	14.3 in [36.4 cm]
Display Tilt	+ 30 / - 30
Swivel / Pivot	+30/ -30
Display Rotation	360

Physical Characteristics

Color	Black
Material	Steel, Aluminum and Plastic
Product Length	34.3 in [87.0 cm]
Product Width	5.3 in [13.5 cm]
Product Height	20.3 in [51.5 cm]
Weight of Product	10.8 lb [4.9 kg]

Packaging Information

Package Length	18.8 in [47.8 cm]
Package Width	9.8 in [24.8 cm]
Package Height	4.7 in [12.0 cm]
Shipping (Package) Weight	12.5 lb [5.6 kg]

What's in the Box

Included in Package	Column
	VESA Adapters
	Cable-Management Clips (Column)
	Monitor Arms
	End Caps
	Cable-Management Clips (Monitor Arm)



End-Cap Screws

Desk-Mount Clamp

Hex Key

Hex Key Screwdriver

M4x14 Screws

M5x14 Screws

Flat Washers

Grommet-Mounting Adapter

Grommet-Mount Plate

Rubber Pads

Instruction Manual

****Product appearance and specifications are subject to change without notice.***

