

## Desk-Mount Dual Monitor Mount - Vertical - Steel

**Product ID:** ARMDUALV



This sturdy and sleek desk-mount dual-monitor mount raises two displays off the surface of your desk or table, to save space and increase your productivity. With its heavy-duty steel construction, the dual-monitor mount securely holds two monitors each up to 27" or two ultrawide monitors up to 34", stacked vertically.

The vertical dual-monitor mount holds two displays, one above the other, in a vertical configuration. The height of the monitors can be adjusted, along the 27.5" (700 mm) pole.

With the double monitor arm, you can work more comfortably, reducing neck and eye strain without having to look side to side when comparing files or reviewing reference material on your screens. It's ideal for comparing spreadsheets, web design, coding, creating and reviewing files, and many others.

The adjustable monitor stand enables smooth, effortless +45/-45 degree tilt and +45/-45 degree swivel, making it easy to reduce glare and find the perfect viewing angle. It can also rotate a full 360 degrees giving you flexible viewing options.

The steel dual monitor arm supports monitors 13" to 27" each in size, or ultrawide monitors up to 34", with a maximum weight of 22.1 lb. (10 kg) per monitor. The surface finish features a powder coating to help resist scratches.

The computer monitor mount makes it easy to mount your VESA mount compatible displays above your desk, using the included C-clamp or grommet mount. For easier mounting, the VESA mount features notches that let you pre-set the mounting screws. Cable clips keep your cables neatly out of sight.

ARMDUALV is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

- Stack two displays vertically, ideal for comparing documents, web design or coding
- Enhance your productivity in office settings including business, healthcare, financial and real estate
- Save space in your business or home office by stacking monitors vertically

## Features

- Save space by mounting two monitors vertically with this dual monitor mount
- Supports two displays 13" to 27", or ultrawide displays up to 34" (max weight per monitor: 22.1 lb./10 kg)
- The height of the monitors can be adjusted along the 27.5" (700 mm) pole
- Adjust your screen angle easily with +45/-45 degree tilt and +45/-45 degree swivel, plus 360 degree rotation
- Heavy-duty steel construction

---

### Hardware

Warranty	5 Years
Wallmountable	No
# of Displays Supported	2
Orientation	Vertical
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.46 in. (10 - 88 mm) Grommet Clamp: Table Thickness 0.39 - 3.46 in. (10 - 88 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

---

### Performance

Weight Capacity (Per Display)	22.1 lb [10 kg]
Minimum Display Size	13"
Maximum Display Size	27in
Fits UltraWide Displays	Yes



Display Tilt	+ 45 / - 45
Swivel / Pivot	+45 / -45
Display Rotation	360

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	4.7 in [12.0 cm]
Product Width	4.6 in [11.6 cm]
Product Height	35.4 in [90.0 cm]
Weight of Product	7.5 lb [3.4 kg]

---

**Packaging Information**

Package Length	17.2 in [43.8 cm]
Package Width	6.5 in [16.4 cm]
Package Height	4.8 in [12.2 cm]
Shipping (Package) Weight	9.4 lb [4.2 kg]

---

**What's in the Box**

Included in Package	lower pole
	upper pole
	desk clamp
	grommet collar
	VESA monitor mounts
	pole connector
	cable-management clips
	cap
	rubber pads



grommet plate

3 mm hex key

5 mm hex key

6 mm hex key

M4x12 mm screws

M5x12 mm screws

washers

instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

