

10 ft DVI-D Single Link Cable - M/M

Product ID: DVIDSMM10



The DVIDSMM10 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 10ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

• Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards



Hardware

Warranty Lifetime

Connector Plating Nickel

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Aluminum-Mylar Foil with Braid

Industry Standards DVI DDWG Standard

Connector(s)

Connector A DVI-D (19 pin)

Connector B DVI-D (19 pin)

Physical Characteristics

Color Black

Wire Gauge 28 AWG

Cable Length 10.0 ft [3.0 m]

Product Length 10.0 ft [3.0 m]

Product Width 0.0 in [0.0 mm]

Product Height 0.0 in [0.0 mm]

Weight of Product 10.9 oz [308.0 g]

Packaging Information

Package Length 8.7 in [22.0 cm]

Package Width 7.9 in [20.0 cm]

Package Height 1.3 in [32.0 mm]

Shipping (Package) 11.2 oz [317.0 g]

Weight

What's in the Box

Included in Package 10 ft DVI-D Single Link Cable - M/M



*Product appearance and specifications are subject to change without notice.