

Mini DisplayPort to DVI Adapter - Mini DP to DVI-D Converter - 1080p Video - VESA Certified - mDP or Thunderbolt 1/2 Mac/PC to DVI Monitor - mDP 1.2 to DVI Single-Link Dongle

**Product ID:** MDP2DVI



The StarTech.com MDP2DVI Mini DisplayPort DVI Adapter Cable offers a cost-effective DVI/Mini DisplayPort link, letting you connect a DVI computer monitor to a device with a Mini DisplayPort output while saving the expense of upgrading the monitor for compatibility. This Mini DisplayPort adapter is the perfect accessory for any of your MacBook or Microsoft Surface Pro devices with mDP.

MDP2DVI is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing DVI monitor to be used with your new Mini DisplayPort device
- Ideal for using your DVI monitor as a secondary display

### Features

- MINI DISPLAYPORT TO DVI ADAPTER: mDP 1.2 (HBR2) to DVI-I (digital only DVI-D) single-link adapter connects a DVI display/projector; 1920x1200/1080p 60Hz video; EDID/DDC pass-through ensure compatibility between source

& display; VESA DisplayPort Certified

- **HOST COMPATIBILITY:** Passive video converter supports mDP++ source including Thunderbolt 1 & 2 MacBooks, MacBook Air & Mac Mini, Microsoft Surface Pro 1-6, desktops (AMD FirePro/Nvidia Quadro), laptops, mini itx computers, Intel NUC & docks
- **INCREASE PRODUCTIVITY:** Connect a DVI monitor or projector, or add a second display to your workstation using the mDP to DVI adapter dongle Compact design makes it ideal for travel 5" (13cm) attached cable
- **SCREW LOCKING DVI:** Mini DisplayPort to DVI display adapter supports DVI screw locking cable to prevent cable from coming loose or accidental disconnection from DVI displays/projectors Tested with DVI cables up to 25ft mDP male to DVI female connector
- **EASY TO USE:** With no software or drivers required, the Mini DP to DVI converter works with any OS including Windows, Ubuntu and macOS; Compatible with MiniDP devices like TB1/TB2 MacBooks with Mini DisplayPort

---

#### Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No

---

#### Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support

---

#### Connector(s)

Connector A	Mini-DisplayPort (20 pin)
Connector B	DVI-I (29 pin)

---

#### Special Notes / Requirements

System and Cable Requirements	DP++ (DisplayPort++) port required from video card or video source for DVI and HDMI signal pass-through
-------------------------------	---

---

#### Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)



Humidity	10%-85% RH
----------	------------

---

**Physical Characteristics**

Color	Black
Cable Length	5.1 in [13 cm]
Product Length	7.3 in [18.5 cm]
Product Width	1.4 in [35.0 mm]
Product Height	0.4 in [11.0 mm]
Weight of Product	1.1 oz [31.0 g]

---

**Packaging Information**

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.7 in [18.0 mm]
Shipping (Package) Weight	1.4 oz [40.0 g]

---

**What's in the Box**

Included in Package	Mini-DisplayPort to DVI Converter
---------------------	-----------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

