

4-Port PCI Express USB 3.0 Card

Product ID: PEXUSB3S42



Here's a cost-effective solution for adding USB 3.0 connectivity to your computer. This 4-port PCIe USB 3.0 card gives you three external ports and one internal port, for the ultimate connection flexibility.

With three external USB 3.0 ports you can connect more devices to your computer. The card provides easy access to commonly-used peripherals such as your tablet and external hard drive. It also features an internal USB port that lets you connect a device such as a flash drive inside your computer case, providing added security and convenience.

USB 3.0 gives you fast access to your files with data transfer rates up to 5 Gbps. Plus it's backward compatible with USB 2.0 and 1.x devices, which eliminates the cost and aggravation of upgrading your existing devices.

Setup is a breeze with native operating system support. The USB 3.0 adapter card automatically installs in Windows 8.1, 8 and 7.

For convenient installation, this PCI Express USB 3.0 card features a dual-profile design that can be installed in almost any type of computer. It comes equipped with a standard profile bracket and also includes a low-profile bracket for installation in small form-factor/half-height systems.

This high-performance USB 3.0 card is enhanced with UASP support, which can perform ~70% faster read speed and ~40% faster write speed over traditional USB 3.0, when paired with .

The PEXUSB3S42 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Note: UASP (USB Attached SCSI Protocol) is supported in Windows 8.1, 8, Server 2012 and Linux kernel 2.6.37 or later. Test results were obtained using an Intel Ivy Bridge system, StarTech.com add-on USB 3.0 cards, a UASP-enabled StarTech.com enclosure, and a SATA III solid state drive.

Certifications, Reports and Compatibility



Applications

- Enhance the connection capabilities of your PCI Express enabled computer or server
- Connect external hard drives, tablets, smartphones, CD/DVD drives, webcams or game controllers to your computer
- Connect your flash drive or other devices to the internal USB 3.0 port for a secure connection

Features

- Expands your computer connectivity with four extra USB 3.0 ports (3 external, 1 internal)
- Easy to install with native OS support in Windows 8.1, 8, 7, and Linux kernel 2.6.31 or later
- Fits standard or small form-factor computers, low-profile bracket included
- Data transfer rates up to 5 Gbps plus UASP support
- Backward compatible with USB 2.0 and 1.x devices
- Built-in optional SATA power connector provides up to 900mA per USB port
- PCIe x1 interface, compliant with PCI Express 2.0 specifications

Hardware		
	Warranty	2 Years
	Ports	4
	Interface	USB 3.0
	Bus Type	PCI Express
	Card Type	Standard Profile (LP bracket incl.)
	Port Style	Integrated on Card
	Industry Standards	USB 3.0 Specification Rev. 1.0 br/>PCI Express Base Specification Rev. 2.0 br/>Intel xHCI Specification Rev. 1.0
	Chipset ID	VIA/VLI - VL805
Performance		
	Maximum Data Transfer Rate	5 Gbps
	Maximum Cable Length	9.8 ft [3 m]
	Type and Rate	USB 3.0 - 5 Gbit/s



	UASP Support	Yes
	MTBF	24,000 hours
Connector(s)		
	Connector Type(s)	PCI Express x1
	Internal Ports	SATA Power (15 pin)
		USB Type-A (9 pin) USB 3.0 (5 Gbps)
	External Ports	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Software		
	OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10
		Windows Server 2008 R2, 2012, 2012 R2, 2016, 2019
		Linux 2.6.31 to 4.11.x <i>LTS Versions only</i>
Special Notes / Requirements		
	System and Cable Requirements	PCI Express enabled computer or server with an available PCI Express x1 slot or higher (x4, x8, x16)
		SATA power connector (recommended, but optional)
	Note	The maximum throughput of this card is limited by the bus interface. If used with PCI Express Gen 1.0 enabled computers, the max throughput is 2.5 Gbps. If used with PCI Express Gen 2.0 enabled computers, the max throughput is 5 Gbps.
Environmental		
	Operating Temperature	5C to 50C (41F to 122F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	20~80% RH
Physical Characteristics		
	Material	Steel
	Product Length	3.4 in [87 mm]
	Product Width	0.7 in [19 mm]
	Product Height	4.7 in [12 cm]



	Weight of Product	1.9 oz [55 g]
Packaging Information		
	Package Length	5.7 in [14.4 cm]
	Package Width	6.7 in [17.1 cm]
	Package Height	1.2 in [30 mm]
	Shipping (Package) Weight	5.0 oz [141 g]
What's in the Box		
	Included in Package	4 Port PCI Express USB 3.0 Card
		Low-Profile Bracket
		Driver CD
		Instruction Manual

*Product appearance and specifications are subject to change without notice.

