

15m Active DisplayPort Cable - DP to DP M/M

**Product ID:** DISPL15MA



The DISPL15MA 15m Active DisplayPort Cable features a built-in active signal booster for a connection distance of up to 50 feet (15m) between your DisplayPort-enabled devices - more than double the DisplayPort connection distance limitation of 16ft, with no signal loss.

This durable yet lightweight active DP cable features a thinner 32 AWG wire construction that allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the DisplayPort signal with no external power needed.

The 15m cable offers a bandwidth of 10.8 Gbps with support for maximum resolutions up to WQXGA (25601600) and optional audio support. The cable is both HDCP and DPCP capable, which ensures that digitally protected content is displayed properly.

This 15-meter Active DisplayPort cable is backed by StarTech.com's 2-year Warranty.

**Please Note:** This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the DisplayPort connectors, in order to ensure that the display device (monitor, projector etc.) and the DisplayPort source are connected properly.

## Certifications, Reports and Compatibility

### Applications

- Connecting a DisplayPort display to a PC or alternative DisplayPort source, over long distances, with no signal loss

### Features

- 1x DisplayPort male connector

- 1x DisplayPort male connector with Latches
- Built-in, active amplifier circuitry
- Offers 50 feet (15 meters) in cable length
- Supports resolutions up to WQXGA (25601600)
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Designed and manufactured to DisplayPort standards
- Thin, high-quality 32 AWG wire construction

---

#### Hardware

Warranty	2 Years
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

---

#### Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

---

#### Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-20C to 70C (-4F to 158F)

---

#### Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	32 AWG
Cable Length	49.2 ft [15 m]
Product Length	49.2 ft [15 m]



Weight of Product 22.6 oz [641 g]

---

**Packaging Information**

Package Quantity 1

Package Length 13.0 in [33 cm]

Package Width 10.0 in [25.5 cm]

Package Height 1.8 in [46 mm]

Shipping (Package) Weight 23.2 oz [658 g]

---

**What's in the Box**

Included in Package 15m Active DisplayPort Cable - M/M

---

***\*Product appearance and specifications are subject to change without notice.***

