

2-port KVM Switch with Dual VGA - USB 2.0

**Product ID:** SV231DVG AU2A



This USB KVM lets you connect two computers, each with dual VGA outputs, to a dual-monitor workstation. You can switch the workstation between each computer, as well as two additional USB peripheral devices and 3.5mm speakers & microphone.

With support for two VGA video inputs and two different computers, this KVM switch maximizes productivity. Not only can you access multiple computers, but you can also use two VGA monitors on each computer streaming independent content to each display, which gives you the freedom to multitask and increase your productivity. The VGA ports support resolutions up to 1920x1200 for maximum screen viewing space.

Featuring dual video and support for your keyboard and mouse, along with a 2-port USB hub for two additional peripheral devices, this KVM switch is perfect for accessing two separate systems using the same workstation. Support for your workstation plus two additional peripheral devices makes this KVM ideal for server control, simplifying access to multiple computer systems.

This 2-port KVM ensures effortless operation with intuitive hotkey control. It provides a simple yet comprehensive solution for switching between each connected computer and also supports manual operation using the easy-to-access buttons located on the front of the switch.

The SV231DVG AU2A is TAA compliant and backed by a 2-year StarTech.com warranty with free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

- Control two computers each with dual-head video cards, from a single workstation, to increase your productivity at the office

- Work with multimedia applications such as video and photo editing
- Operate multiple computers in manufacturing lines
- Install in your server room, for multi-computer access

## Features

- Maximum productivity with dual-display and multi-computer access
- Hassle-free operation with hotkey and push-button switching
- Share your USB peripheral devices with built-in 2-port USB hub
- Supports resolutions up to 1920x1200
- 3.5mm speaker and microphone console support

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	2
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

---

### Performance

On-Screen Display	No
DVI Support	No
IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	1920 x 1200



Supported Resolutions	up to 1920 x 1200
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
MTBF	72000 hours

---

#### Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position) USB Type-A (4 pin) USB 2.0
Host Connectors	VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position) USB B (4 pin)

---

#### Indicators

LED Indicators	PC Selection Indicators Green - PC Detected Green - Power Red - PC Indicator
----------------	---

---

#### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.6A
Output Voltage	12V DC
Output Current	1.5A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	18



---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	90% RH

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	6.3 in [15.9 cm]
Product Width	4.1 in [10.4 cm]
Product Height	2.2 in [57.0 mm]
Product Depth	5.1 in [13 cm]
Weight of Product	27.1 oz [768.0 g]

---

**Packaging Information**

Package Length	7.4 in [18.7 cm]
Package Width	9.5 in [24.1 cm]
Package Height	3.6 in [92.0 mm]
Shipping (Package) Weight	2.6 lb [1.2 kg]

---

**What's in the Box**

Included in Package	dual VGA USB KVM switch
	universal power adapter (NA / EU / UK / AU)
	instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

