

Cisco GLC-LH-SMD Compatible SFP Module - 1000BASE-LH - 1GbE Single Mode Fiber SMF Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 20km - 1310nm - DDM Cisco Firepower, IE2000, IE4000

**Product ID:** SFPG1320C



The SFPG1320C is a Cisco GLC-LH-SMD compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-LH compliant networks, with a maximum distance of up to 20 km (12.4 mi).

Technical Specifications:

- Wavelength: 1310nm
- Maximum Data Transfer Rate: 1.25 Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 20 km (12.4 mi)
- MTBF: 2,722,277 hours
- Power Consumption: Less than 1 Watt
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

### Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

### Features

- **100% CISCO GLC-LH-SMD COMPATIBLE:** Works with Cisco switches like Firepower, IE2000, IE4000, C9300, IE3000 and others
- **TECHNICAL SPECS:** 1000BASE-LH 1 Gbps Single Mode (SMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 20km (12.4mi)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

---

#### Hardware

Warranty	Lifetime
Compatible Brand	Cisco
WDM	No
Industry Standards	IEEE 802.3z 1000BASE-LH

---

#### Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	20 km (12.4 mi)
Type	Single Mode
Wavelength	1310nm
Fiber Operating Mode	Half/Full-Duplex



DDM	Yes
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	2,722,277 hours
Power Consumption (In Watts)	< 1 W

---

#### Connector(s)

Local Unit Connectors	Fiber Optic LC Duplex
-----------------------	-----------------------

---

#### Special Notes / Requirements

Note	For use in Gigabit fiber networking equipment and media converters
------	--

---

#### Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	30~70% RH

---

#### Physical Characteristics

Product Length	2.4 in [60.0 mm]
Product Width	0.5 in [12.0 mm]
Product Height	0.4 in [10.0 mm]
Weight of Product	0.7 oz [20.0 g]

---

#### Packaging Information

Package Length	3.6 in [92.0 mm]
Package Width	4.6 in [11.8 cm]
Package Height	1.3 in [33.0 mm]
Shipping (Package) Weight	1.7 oz [48.0 g]

---

#### What's in the Box

Included in Package	1.25 Gbps Single Mode LC SFP
---------------------	------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

