

### 10 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

#### Product ID: DVIIDMM10



The DVIIDMM10 10ft DVI-I Dual Link cable features 2 male DVI-I (29-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 10ft DVI-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

# Certifications, Reports and Compatibility

## **Applications**

• Connect your desktop or laptop computer to a DVI-I Dual Link display or projector

### **Features**

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices



• Compliant with DVI DDWG Standards

• Supports both analog and digital displays

**Hardware** Warranty Lifetime **Industry Standards DVI DDWG Standard Performance** Maximum Data Transfer 9.9 Gbits/sec Rate Connector(s) Connector A DVI-I (29 pin) Connector B DVI-I (29 pin) **Physical Characteristics** Color Black Wire Gauge 28 AWG Cable Length 10.0 ft [3.0 m] **Product Length** 10.0 ft [3.0 m] Weight of Product 15.8 oz [449 g] **Packaging** Information Package Length 15.6 in [39.5 cm] Package Width 5.5 in [14 cm] Package Height 0.9 in [22 mm] Shipping (Package) 16.2 oz [458 g] Weight What's in the Box

10 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Included in Package

<sup>\*</sup>Product appearance and specifications are subject to change without notice.