

USB C Multiport Video Adapter with HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 1.4 or mDP 1.2 (4K) - VGA or DVI (1080p) - Rose Gold Aluminum

Product ID: CDPVDHDMDPRG



This rose gold USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI or Mini DisplayPort display. The adapter is also available in silver (CDPVGDVHDMDP) and space gray (CDPVDHDMDPSG).

Avoid the hassle of carrying different adapters for different displays with this 4-in-1 USB-C adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The USB Type-C adapter has an aluminum housing designed to match your rose gold MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

The CDPVDHDMDPRG is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- · Connect to virtually any display while traveling
- Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook



Features

- 4-IN-1 MULTIPORT USB-C VIDEO ADAPTER: USB-C DP Alt Mode to any one of HDMI 1.4 (4K 30Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible
- TOUGH & PORTABLE: Durable aluminum Rose Gold enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms
- COMPATIBILITY: USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Laptop 3/Surface Book 3, TB3 MacBook Pro/Air, HP EliteBook/Spectre/ZBook, Chromebooks
- TESTED & VERIFIED: USB Type-C adapter tested @ 4K mini DisplayPort (60Hz)/HDMI (30Hz) or 1080p VGA/DVI with TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- EASY TO USE: Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

Hardware

Warranty 3 Years

Active or Passive Adapter Active

AV Input USB-C

AV Output DVI-I (Digital Only) - Single-Link

HDMI - 1.4

VGA

Mini DisplayPort - 1.2

Chipset ID Cypress - CYPD1120

Cypress - CY7C65210

Parade - PS8348B

Parade - PS171

Performance

Maximum Cable Distance 49.9 ft [15.2 m]

To Display

Maximum Analog Resolutions

1920 x 1200 @ 60Hz

Maximum Digital

3840 x 2160 @ 30Hz

Resolutions



Supported Resolutions Max HDMI output: 3840 x 2160 @ 30Hz

Max mDP output: 3840 x 2160 @ 60Hz

HDMI and mDP output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920

x 1080, 1280 x 720

DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720

Wide Screen Supported Yes

Audio Specifications HDMI - 7.1 Channel Audio

DVI - No Audio Support

VGA - No Audio Support

Mini DisplayPort - 5.1 Channel Audio

MTBF 654,111 hours

Connector(s)

Connector A USB-C (24 pin) DisplayPort Alt Mode

Connector B Mini-DisplayPort (20 pin)

VGA (15 pin, High Density D-Sub)

DVI-D (25 pin)

HDMI (19 pin)

Special Notes / Requirements

Note Only one video output is supported on the video adapter at a time, if

multiple connections are made, only one of the outputs will function

Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

Environmental

Operating Temperature 0C to 45C (32F to 113F)

Storage Temperature -10C to 70C (14F to 158F)



Humidity	Storage: 5% ~ 90 % RH ((no condensation)

Operating: 10% ~ 85 % RH (no condensation)

Physical Characteristics		
	Color	Rose Gold
	Material	Aluminum
	Cable Length	4.5 in [11.5 cm]
	Product Length	6.7 in [16.9 cm]
	Product Width	5.6 in [14.2 cm]
	Product Height	0.6 in [15.0 mm]
	Weight of Product	6.4 oz [180.0 g]
Packaging Information		
	Package Length	2.2 in [55.0 mm]

4.1 in [10.5 cm]

0.6 in [16.0 mm]

3.5 oz [100.0 g]

What's in the Box

Included in Package travel A/V adapter

Package Width

Package Height

Shipping (Package) Weight

^{*}Product appearance and specifications are subject to change without notice.