

## **10m DVI-D Dual Link Cable – M/M**

*StarTech ID: DVIDDMM10M*



The DVIDDMM10M 10m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 10 meters in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 10m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### **Applications**

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

### **Features**

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector Plating	Nickel
Fire Rating	CMG Rated (General Purpose)
Industry Standards	DVI DDWG Standard
Number of Ferrites	2
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Cable Length	10 m [32.8 ft]
Cable OD	8.6 mm [0.3 in]
Color	Black
Connector Style	Straight
Product Weight	920 g [32.5 oz]
Wire Gauge	28 AWG
Package Quantity	1
Shipping (Package) Weight	940 g [33.2 oz]
Included in Package	1 - 10m DVI-D Dual Link Digital Video Monitor Cable - M/M

Certifications, Reports and Compatibility

