



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

## Beaumont LED Outdoor Flush Mount BMF Series

### Features

This Beaumont LED ceiling fixture is highly decorative style adding beauty and light to any room or spaces. An excellent alternative solution to incandescent or CFL fixture with long lasting and energy saving LED technology. Ideal use for general lighting in indoor or outdoor residential, commercial, and hospitality applications. Fixture can be mounted to a standard junction box (not included) on a wall or ceiling. Available in multiple sizes and finishes.

### Construction

Stainless steel housing with aluminum die-cast trim and painted in weather resistant powder coating over molded diffuser. Back pan is made from 12 gauge stamped aluminum material with matching powder coat finish. Power supply connections must be made inside a junction box (not included).

### Finish

Available in textured grey or bronze finish.

### Diffuser

Diffuser is made of 0.080" thick standard white acrylic.

### Electrical

Input 120-277VAC / 60Hz.  
Compatible with 0-10V dimmers.

### LED

Integrated LED modules capable of producing:  
8" - 21W, 1600 source lumens  
12" - 29W, 2800 source lumens  
3000K, 3500K, 4000K Adjustable (CCT).  
Rated for 50,000 Hrs. 90 CRI.

### Certification

All fixtures are cETLus listed for outdoor wet locations.  
ADA

### Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date-of-purchase.

**Specifications and dimensions  
subject to change without notice.**



**3in1** color temperature  
3000K/3500K/4000K



## Ordering Information:

Textured Grey	LED	Source Lumens	Adjustable CCT	DIA.	H
BMF0816LAJD2TG	21W	1600	3000K/3500K/4000K	8"	3-3/4"
BMF1228LAJD2TG	29W	1600	3000K/3500K/4000K	12"	3-3/4"

Textured Bronze	LED	Source Lumens	Adjustable CCT	DIA.	H
BMF0816LAJD2BZ	21W	2800	3000K/3500K/4000K	8"	3-3/4"
BMF1228LAJD2BZ	29W	2800	3000K/3500K/4000K	12"	3-3/4"