



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Beverly LED Outdoor Pendant BVYP Series

Features

This outdoor LED light is ideal for security and general lighting. Fixture mounts to standard junction box (not included).

Construction

Die-cast aluminum construction. Standard mounting holes and hardware are included. Power supply connections must be made inside a junction box (not included). Canopy - 1-3/4" H x 6" DIA.

Finish

Black powder coated or Satin Nickel finish.

Diffuser

Clear glass diffuser.

Electrical

Input 120-277 VAC 60 HZ.
0-10V dimming (120-277V), TRIAC (120V).
Minimum starting temp -4° F / -20°C

Lamping

Fixture includes a LED modules capable of producing:
9W = 630 delivered lumens
Adjustable Choice 2700K, 3000K, 3500K, 4000K, 5000K (CCT).
Rated for 50,000 Hrs., 90 CRI.

Certification

All fixtures are cETLus listed for wet locations.
Title 24/JA8 Compliant

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date of purchase.

Specifications and dimensions
subject to change without notice.



Ordering Information:

Black BVYP06LAJUBK	Satin Nickel BVYP06LAJUDSN	LED 9W	Delivered Lumens 630	Adjustable CCT 2700K/3000K/3500K/4000K/5000K	DIA. H 2-1/2" 6-1/4"
-----------------------	-------------------------------	-----------	-------------------------	---	-------------------------